

6			5		4		3		2		1	
ITEM	PART#	DESCRIPTION	QTY	UOM				FROM	TO	DESCRIPTION	COLOR	
A	430200800	MicroFit 3.0 Plug DR PnlMnt 8Ckt	1	PC				A1	—	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK	
B	430310023	MICROFIT 3.0 M CRP TERM CHN 30AU 18AWG	8	PC				A2	—	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK	
C	—	PAPER PRINTED PAPER WHITE	1	PC				A3	—	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK	




TABLE			
PART NUMBER	L1	L2	TITLE
2147582081	150±8	63REF	MICRO-FIT3.0 P-S 8 CIRCUIT 150MM Au
2147582082	300±10	138REF	MICRO-FIT3.0 P-S 8 CIRCUIT 300MM Au
2147582083	600±10	287REF	MICRO-FIT3.0 P-S 8 CIRCUIT 600MM Au

- NOTES
- Connector view shown is from mating side.
 - Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 1.39mm Max.
 - Label text must be 2mm max. in height with Arial font.
 - Label must be wrapped on the cables.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
30/12/2019	A	INITIAL RELEASE	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC:			
▽ = 0		mm		NTS		EC NO: 629791 DRWN: ARAJU 2019/12/30 CHK'D: RDESAI01 2020/01/18 APPR: RDESAI01 2020/01/18			
▽ = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)							
▽ = 0		ANGULAR TOL ± °							
▽ = 0		4 PLACES		±		SEE TABLE			
▼ = 0		3 PLACES		±					
▽ = 0		2 PLACES		±					
▽ = 0		1 PLACE		±		PRODUCT CUSTOMER DRAWING			
☒ = 0		0 PLACES		±					
■ = 0		INITIAL REVISION:							
▽ = 0		DRWN: ARAJU 2019/12/30		APPR: RDESAI01 2020/01/18		DOCUMENT NUMBER			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES	
						A4-SIZE		214758	
						MATERIAL NUMBER		CUSTOMER	
						SEE TABLE		GENERAL MARKET	
								SHEET NUMBER	
								1 OF 1	

DOCUMENT STATUS	P1	RELEASE DATE	2020/01/18	09:07:19
-----------------	----	--------------	------------	----------