

6		5			4		3		2		1	
ITEM	PART#	DESCRIPTION			QTY	UOM			FROM	TO	DESCRIPTION	COLOR
A,B	430250800	MicroFit 3.0 DR Rcpt 8Ckt			2	PC			A1	B4	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
C	430300040	MicroFit 3.0 F Crp Term Chn 30Au 18			16	PC			A2	B3	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
D	---	PAPER PRINTED PAPER WHITE			1	PC			A3	B2	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
									A4	B1	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
									A5	B8	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
									A6	B7	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
									A7	B6	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK
									A8	B5	1X18AWG DISC PVC BK UL1061 HOOKUP	BLACK




TABLE			
PART NUMBER	L1	L2	TITLE
2147552081	150±8	63REF	MICRO-FIT3.0 R-R 8 CIRCUIT 150MM Au
2147552082	300±10	138REF	MICRO-FIT3.0 R-R 8 CIRCUIT 300MM Au
2147552083	600±10	287REF	MICRO-FIT3.0 R-R 8 CIRCUIT 600MM Au

NOTES

1. Cable assembly must pass 100% continuity and polarity test.
2. Connector view shown is from mating side.
3. Label text must be 2mm max. in height with Arial font.
4. Label must be wrapped on the cables.

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

DOCUMENT STATUS	P1	RELEASE DATE	2020/01/18	09:07:04
-----------------	----	--------------	------------	----------

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC:			molex		
▽ = 0	mm		NTS							
▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)									
▽ = 0	ANGULAR TOL ± °				EC NO: 629791 DRWN: ARAJU					