

5

4

3

2



1

D



C

B

A



Kontakt für Schlauchinnendurchmesser 4,0 mm
tube fitting insert for tubing size ID 4,0 mm

 All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Masse/ Free size tolerances		
				Dat.	Name	Massstab/Scale 2:1	Han-Modular Pneumatikstiftkontakt <i>pneumatic male tube fitting insert</i>	
			Detail.	20.10.98	SPER			
			Insp.		SDT			
			Stand.					
27321	07.03.00	Gü	HARTING KGaA D-32339 ESPELKAMP				TB 09 14 000 6153	
Mod.	Dat.	Name					Sub. TB 09 14 000 6... v. 23.06.94	
							Blatt/ page	