









Printed Board Layout
Component side



1) Einlötlstifte passend für Lochungen
Ø1 ±0,1 nach IEC 60326-3
Solder pins for PCB connections
Ø1 ±0,1 as per IEC 60326-3
A souder pour des trous de Ø1 ±0,1
selon IEC 60326-3

A	09185507911	3	4,5	 All Dimensions in mm Original Size DIN A 3	Techn. Character.				Nicht tolerierte Maße/ Free size tolerances		
	09185506911	2	4,5								
	09185505911	0,76 µm Au	4,5							SEK 18 Male xonconnector Standard 50 poles Angled pins Short locking levers	
	09185507913	3	2,9					Detail.	01-DEC-99		Th
	09185506913	2	2,9		29753	11-MAR-02	JB	Insp.	03-DEC-01		JMV
	09185505913	0,76 µm Au	2,9		29739	03-DEC-01	JB	Stand.			
Bestell-Nr. Part-No. Reference	Anforderungsstufe performance level Niveau de qualite	a		27931	15-JUNE-00	JB	HARTING EURL F-95972 Paris			TB 0918550x91x	Blatt/ page 2/2
				26554	01-DEC-99	JB				Sub.	
				Mod.	Dat.	Name					