









View from ◎ direction



Measurable cable diameter



寸法許容差 Tolerance(±mm)						
	精	上	中	並	粗	
1~4	0.05	0.1	0.1	0.2	0.3	
~16	0.07	0.1	0.2	0.3	0.5	
~63	0.1	0.2	0.3	0.5	0.7	
~250	0.2	0.3	0.5	0.7	1.2	
~1000	0.3	0.5	0.7	1.5	2.0	
全長	0.5	0.5	0.5	0.5	0.5	

材質	—		
Material	—		
処理	—		
Finish	—		
承認	2015/12/02	永井明博	フェライトコア変更
承認	2001/02/15	永井明博	新規作成
設計	永井明博	設計	Designed by
注記	Description		

CAD data: 9661A040_04_OUTLINE DRAWING			
承認	Approved by	投影法	Projection method
戸井 順	戸井 順	第一角法	First angle projection
検図	Checked by	尺寸	Scale
戸井 順	戸井 順	1:1	1:1
設計	Designed by	単位	Unit
永井明博	永井明博	mm	mm
図番	Draw No.	シート	Sheet
9661A040	9661A040	1/1	1/1
版	Rev.	04	04