

UNCONTROLLED DOCUMENT


NOTES:

PARTS ARE PACKAGED 100 PIECES PER BAG.

DRILLED HOLE DIAMETER [6.00 MM] .236

MAX. PANEL THICKNESS [3.20 MM] .125

MAX. STRENGTH [22.20 KG] 50 LBS.



TOLERANCES UNLESS NOTED

±.005 ON DIMENSIONS THRU .625

±.008 ON DIMENSIONS .626 THRU 1.000

±.010 ON DIMENSIONS 1.001 THRU 1.500

±.015 ON DIMENSIONS LARGER THAN 1.500

±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF
MICRO PLASTICS INC.

CATALOG DRAWING
PUSH MOUNT CABLE TIE
MICRO P/N NTA20347PMTG
DWG. # NTA20347PMTG
FILE SERVER\ENG\WEB

MATERIAL: 6/6 NYLON

DATE

SCALE
1:1

DSB