




UNCONTROLLED DOCUMENT

NOTE:
MOUNTING HOLE: $\phi .500$
MAX PANEL THICKNESS: .125



TOLERANCES UNLESS NOTED

- $\pm .005$ ON DIMENSIONS THRU .625
- $\pm .008$ ON DIMENSIONS .626 THRU 1.000
- $\pm .010$ ON DIMENSIONS 1.001 THRU 1.500
- $\pm .015$ ON DIMENSIONS LARGER THAN 1.500
- $\pm .015$ ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF		
MICRO PLASTICS INC.		
CATALOG DRAWING OPEN/CLOSE BUSHING MICRO P/N NM22OCB0500 DWG. # NM22OCB0500 FILE SERVER\ENG\WEB		
MATERIAL:		NYLON 6/6; BLACK
DATE	SCALE 3:1	DB