



SPECIFICATIONS:

Material Properties:

- Dissipative Polyvinylchloride (PVC)
- Material Thickness: 0.012" (1S) front & back
- Material Tolerance (thickness): +/-10%
- Material Finish: Matte
- ESD Protective Symbol imprinted along top flap in bottom right corner
- Embossed with Desco & Made In America along bottom of pocket protector on the back

Electrical Properties:

- Rs: 1×10^6 to $< 1 \times 10^{11}$ ohms per ANSI/ESD STM11.11

Item	Size (W x L)	Description	Smock Sizes
07475	5 1/8" x 7"	ESD Pocket Protector	XSmall - Medium
07476	6 1/2" x 8"	ESD Pocket Protector	Large - 6XLarge

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." [ESD Handbook ESD TR20.20 section 2.4 Sources of Static Electricity]



Made in the
United States of America

Specifications and procedures are subject to change without notice

ESD POCKET PROTECTOR

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEBSITE: Desco.com
PHONE (909) 627-8178

DESCO EAST: ONE COLGATE, CANTON, MA 02021-1407
PHONE (781) 821-8370

**DRAWING
NUMBER**

07475

DATE

June
2014

Dimensional tolerances are +/- 1/16" unless specified

Drawing is not to scale