

THIS IS A C.A.D. GENERATED DRAWING **TOLERANCE** UNLESS OTHERWISE SPECIFIED DO NOT MAKE MANUAL REVISIONS TO MASTER. .X ±0.25

.XX ±0.13 .XXX ±0.05




ISSUE NUMBER ORIGINAL

NOTES:

CURRENT RATING: 2A AC/DC **VOLTAGE RATING:** 100V AC/DC **TEMPERATURE RATING:** -40°C ~ 105°C **CONTACT RESISTANCE:** $10m\Omega$ MAX. **HOUSING RESISTANCE:** $1000M\Omega$ min. WITHSTANDING VOLTAGE: 800V AC / 60s

HOUSING MATERIAL: NYLON PA66, UL94V-0



1.2~1.6 **PCB THICKNESS**

140 SERIES RIGHT ANGLE PCB MOUNT

THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC TORONTO, ONTARIO CANADA

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC..AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 140 Assembly	
DRAWN: C.B	DATE: March 27, 2020
CHECKED:	DATE:
SCALE: 5:1	SHEET 1 OF 1

ISSUE DRAWING NUMBER: 140 Assembly 1 PART NUMBER: 140-508-415-000