



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-014654	06SEP2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB


D



2320922-2
SCALE 2:1




2320922-3
SCALE 2:1




2320922-4
SCALE 2:1

C




B

A




SECTION A-A



SECTION A-A

- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: RUST
- 4 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: ORANGE
- 5 MATERIAL: SILICONE
COLOR: TAN
6. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
7. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT:
A. 2292799-1 SMOOTH WIRE EXIT
B. 2292799-2 NC16/NW13 CONDUIT WIRE EXIT
C. 2292799-3 NC12/NW10 CONDUIT WIRE EXIT
- 90° EXIT:
D. 2302492-1 SMOOTH WIRE EXIT
E. 2302492-2 NC16/NW13 CONDUIT WIRE EXIT
F. 2302492-3 NC12/NW10 CONDUIT WIRE EXIT
8. RECOMMENDED SEAL PLUG: 776363-1
9. MATING CONNECTOR: 2320928-X



D	ORANGE	2320934-4
C	PURPLE	2320934-3
B	BLUE	2320934-2
A	TAN	2320934-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MCNEAL 03APR2018	TE Connectivity			
		CHK R. BALTER 03APR2018				
		APVD R. BALTER 03APR2018	NAME PLUG ASSEMBLY, 4 POSITION REDUCED DIA SEAL, HIGH TEMP, AMPSEAL 16			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-2184		SIZE CAGE CODE DRAWING NO	
		0 PLC ±	APPLICATION SPEC 114-13065		RESTRICTED TO	
		1 PLC ±	WEIGHT 12.5±1g		SCALE 1:1 SHEET OF	
		2 PLC ±0.20	Customer Drawing		REV A1	
		3 PLC ±				
		4 PLC ±				
		ANGLES ±				
MATERIAL		FINISH				