



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-013881	27AUG2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB


D



2320933-2
SCALE 2:1
KEY B




2320933-3
SCALE 2:1
KEY C




2320933-4
SCALE 2:1
KEY D

C




2320933-1 SHOWN
KEY A

B




SECTION A-A

A



SECTION A-A

- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: RUST
- 4 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: ORANGE
- 5 MATERIAL: SILICONE
COLOR: TAN
6. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
7. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT:
- A. 2292798-1 SMOOTH WIRE EXIT
- B. 2292798-2 NC12/NW10 CONDUIT WIRE EXIT
- C. 2292798-3 NC08/NW7.5 CONDUIT WIRE EXIT
- 90° EXIT:
- D. 2302491-1 SMOOTH WIRE EXIT
- E. 2302491-2 NC12/NW10 CONDUIT WIRE EXIT
- F. 2302491-3 NC08/NW7.5 CONDUIT WIRE EXIT
8. RECOMMENDED SEAL PLUG: 776363-1
9. MATING CONNECTOR: 2320927-X.



SCALE 2:1

D	ORANGE	2320933-4
C	PURPLE	2320933-3
B	BLUE	2320933-2
A	TAN	2320933-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MCNEAL 07FEB2018	TE Connectivity			
DIMENSIONS:		CHK R. BALTER 07FEB2018				
mm		APVD R. BALTER 07FEB2018	NAME PLUG ASSEMBLY, 3 POSITION, REDUCED DIA SEAL, HIGH TEMP, AMPSEAL 16			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-2184	SIZE A2			
0 PLC ±		APPLICATION SPEC 114-13065	CAGE CODE -			
1 PLC ±		WEIGHT 8g	DRAWING NO C-2320933			
2 PLC ±0.30		CUSTOMER DRAWING	RESTRICTED TO -			
3 PLC ±		SCALE 4:1	SHEET OF			
4 PLC ±			REV A1			
ANGLES ±1°						
FINISH						