


240.0 [9.45] 229.78 [9.05] Inlay Length 179.78 [7.08] [7.48]

End View of Assembly






SECTION D-D (Side View of Assembly)



Removable Panel



Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory mjm@hammondmfg.com for quotes
Solid models of this enclosure available in STEP or IGES.

(Part number and text placement/orientation on our products are subject to change, we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes top and bottom cover, 1 removable panel, battery door battery spring clips (8 pcs), 9V adapter (2 pcs) and 6 cover screws (M3-0.5 x 18mm). M3 Brass inserts are installed for cover screws. Enclosure molded from FR ABS (UL94-V0).

Recommended Cover Screw Torque - 43-50 ozf.in (30-35cN-m)

PART NUMBERS	
1599TABLBAT Enclosure	
Black Enclosure	1599TABLBKBAT
Grey Enclosure	1599TABLGYBAT
ACCESSORIES	
Replacement Cover Screws	1594MS100 (Silver)
[M3-0.5 x 18mm] (Pkg 100)	1594MS100BK (Black)
P.C. Board Screws	1593ATS50 (Pkg 50)
(#4 x 1/4" Self Tapping)	1593ATS100 (Pkg 100)
1599TABL End Panel	1599TABLPLBK-B (Black)
(Single Panel)	1599TABLPLGY-B (Grey)
9V Battery Kit	53BATCLIP9V-B
AA Battery Clip Kit (4 positive and 4 Negative)	1553HDR-BKIT



Inside View Top Inside View Bottom 120.0 120.0 [4.72][4.72]55.00 0 0 ⊚. [2.17] 60.0 60.0 140.00 163.92 [2.36] [2.36] [5.51] 0 [6.45] 131.92 80.00 59.5 166.30 134.13 [5.19] [3.15] [2.34] [6.55][5.28] 231.97 [9.13] - (6) 0 55.00 [2.17]PCB Posts x 10 100.0 100.0 Drawings available 25.0 [3.94] [3.94] Accepts #4 x 1/4" for maximum P.C [.98] Self-Tapping Screw Board size for top and bottom

Dimensions: mm [inches]