







PART NUMBER (FROM 20Pos. TO 40Pos.)

10159549-120XXLF ~ 10159549-140XXLF



10159549-132XALF

<p>A CODE / COLOR: BLACK</p> <p>DIM ("A"-1.0)</p>	<p>B CODE / COLOR: GREEN; COLOR CODE: RAL6002</p> <p>DIM ("A"-1.0)</p>
<p>C CODE / COLOR: WHITE; COLOR CODE: RAL9001</p> <p>DIM ("A"-2.4)</p>	<p>D CODE / COLOR: BORDEAUX; COLOR CODE: RAL4004</p> <p>DIM ("A"-2.4)</p>
REMARK, THIS SHEET SHOWS 20Pos. TO 40Pos.	

POS.	PART NO.	DIM "A"	POS.	PART NO.	DIM "A"	POS.	PART NO.	DIM "A"
20	10159549-120XALF	21.70	28	10159549-128XALF	28.90	36	10159549-136XALF	36.10
	10159549-120XBLF			10159549-128XBLF			10159549-136XBLF	
	10159549-120XCFL			10159549-128KCLF			10159549-136XCFL	
	10159549-120XDLF			10159549-128KDLF			10159549-136XDLF	
22	10159549-122XALF	23.50	30	10159549-130XALF	30.70	38	10159549-138XALF	37.90
	10159549-122XBLF			10159549-130XBLF			10159549-138XBLF	
	10159549-122XCFL			10159549-130XCFL			10159549-138XCFL	
	10159549-122XDLF			10159549-130XDLF			10159549-138XDLF	
24	10159549-124XALF	25.30	32	10159549-132XALF	32.50	40	10159549-140XALF	39.70
	10159549-124XBLF			10159549-132XBLF			10159549-140XBLF	
	10159549-124XCFL			10159549-132XCFL			10159549-140XCFL	
	10159549-124XDLF			10159549-132XDLF			10159549-140XDLF	
26	10159549-126XALF	27.10	34	10159549-134XALF	34.30	REMARK, THIS SHEET SHOWS 20Pos. TO 40Pos.		
	10159549-126XBLF			10159549-134XBLF				
	10159549-126XCFL			10159549-134XCFL				
	10159549-126XDLF			10159549-134XDLF				

NOTES:

- 1 - MATERIAL: THERMOPLASTIC UL94V-0
COLOR: FOUR COLORS, DETAIL SEE TABLE
2 - PACKAGING SPEC: GS-14-2668
3 - PART NUMBER CODE: 10159549-1 XX X X LF



NUMBER OF POSITIONS
20 - 20 PINS
22 - 22 PINS
.....
40 - 40 PINS

RoHS COMPATIBLE
CODE OPTION + COLOR
A - A CODE
B - B CODE
C - C CODE
D - D CODE

PACKAGING
K - TRAY PACKAGE
T - PE BAG PACKAGE



mat'l. code	surface ISO 1302	tolerance ISO 406/ISO 1101	projection mm	product family HPL649
ltr	ecn no	dr	date	title
A	NEW DRAWING RELEASE	DW	10/23/20	RECEPTACLE KITS, DUAL ROW, WITH CPA
				Minitek 1.8mm Series Cable Kits
				dwg no
				sheet 1 of 3
				size
				10159549
				A4
				type
				Product Customer Drawing
sheet	revision	A		
index	sheet	1~3		

10159549-114XXLF ~ 10159549-118XXLF









POS.	PART NO.	DIM "A"	POS.	PART NO.	DIM "A"
14	10159549-114XALF	16.30	18	10159549-118XALF	19.9
	10159549-114XBLF			10159549-118XBLF	
	10159549-114XCFL			10159549-118XCFL	
	10159549-114XDLF			10159549-118XDLF	
16	10159549-116XALF	18.10	REMARK, THIS SHEET SHOWS 14Pos. TO 18Pos.		
	10159549-116XBLF				
	10159549-116XCFL				
	10159549-116XDLF				

1 - PE BAG PACKAGE

mat'l. code				surface				tolerance				projection				product family			
				ISO 1302 ✓				ISO 406/ISO 1101								HPL649			
litr ecn no dr date				tolerances unless otherwise specified								title							
A				angles				mm				RECEPTACLE KITS, DUAL ROW,WITH CPA							
				linear								Minitek 1.8mm Series Cable Kits							
				0±2°				scale 1:1											
				dr				NICK ZHANG 10/23/20				dwg no sheet2 of 3 size							
				engr				NICK ZHANG 10/23/20				10159549 A4							
				chr				ZK HU 10/23/20											
				appd				TIM YAO 10/23/20				type Product Customer Drawing							
sheet index				revision sheet 1~3															

PART NUMBER (FROM 10Pos. TO 12Pos.)

10159549-110XXLF ~ 10159549-112XXLF



POS.	A CODE / COLOR: BLACK
10	
12	
REMARK, THIS SHEET SHOWS 10Pos. TO 12Pos. NO B/C/D CODE TO PROVIDE.	

POS.	PART NO.	DIM "A"	POS.	PART NO.	DIM "A"
10	10159549-110XALF	12.70	12	10159549-112XALF	14.50
REMARK, THIS SHEET SHOWS 10Pos. TO 12Pos.					

NOTES:

1 - MATERIAL: THERMOPLASTIC UL94V-0
COLOR: FOUR COLORS, DETAIL SEE TABLE

2 - PACKAGING SPEC: GS-14-2668

3 - PART NUMBER CODE: 10159549-1 XX X X LF

NUMBER OF POSITIONS

10 - 10 PINS

12 - 12 PINS

RoHS COMPATIBLE
CODE OPTION + COLOR
A - A CODE
(NO B/C/D CODE TO PROVIDE.)

PACKAGING
K - TRAY PACKAGE
T - PE BAG PACKAGE

mat'l. code				surface ISO 1302	tolerance ISO 406/ISO 1101	projection mm	product family HPL649
ltr	ecn	no	dr	date	tolerances unless otherwise specified	mm	title
A					angles 0°±2'	linear mm	RECEPTACLE KITS, DUAL ROW, WITH CPA
						scale 1:1	Minitex 1.8mm Series Cable Kits
					dr	NICK ZHANG	10/23/20
					engr	NICK ZHANG	10/23/20
					chr	ZK HU	10/23/20
					appd	TIM YAO	10/23/20
sheet index	revision sheet	A 1~3					Amphenol FCI
							dwg no 10159549
							type Product Customer Drawing
							sheet 3 of 3
							size A4