



1

2




3

4

5


6

view shown without plastic pin and grounding





PC card drilling dimensions(after plating)

(thickness 1.60 ±0.20)




Detail of grounding strip



VIEW FOR 25 POSITION ONLY

GENERAL CHARACTERISTICS AND ROHS INFORMATION:

SEE DRAWING C01-8646-0001

mat'l. code —				surface ISO 1302 ✓			tolerance ISO 406 ISO 1101			projection 		product family D—SUB						
ltr	ecn no	dr	date	tolerances unless otherwise specified									title FEMALE CONNECTOR DELTA-DEUROPE RIGHT ANGLED PRESS FIT					
G	ELX-I-18050	MP	2014/06/23	angles	linear	.0±.0.3												
H	ELX-I-33101	GM	2019-04-01			.00±0.1												
J	ELX-I-34612	GM	2019-20-08			0°±2° .000±0.05												
				dr	PESSON			1996/12/06				dwg no			sheet 1 of 1			size
				engr	GREGAR M			2019-04-01				C01—8646—0522			A3			
				chr	MITHUN PAUL			2019-20-08				type Product Customer Drawing						
				appd	SANOJ P K			2019-20-08										
sheet index		revision sheet		J	1													

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	LEAD FREE	LEAD FREE
09	30.81	24.99	18.00	16.21	10.96	D09S81C4GL00LF	D09S81C6GL00LF
15	39.14	33.32	26.32	24.54	19.18	D15S81C4GL00LF	D15S81C6GL00LF
25	53.03	47.04	40.04	38.25	33.12	D25S81C4GL00LF	D25S81C6GL00LF
37	69.32	63.50	56.50	54.71	49.68	D37S81C4GL00LF	D37S81C6GL00LF
						Gold flash	0.76 µ gold/GxT