



REVISIONS			
SYM	ECN	DESCRIPTION	DATE
A			07/11/07

D-SUB TECHNICAL DATA

SHELL : Steel, 2.5um (100u") min tin over 1.25um (50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0
CONTACTS : brass.
0.76um(30u") min gold over 0.25um(10u") min nickel
ELECTRICAL : Voltage rating :1000 V RMS at 50 Hz
Current rating 5A.
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms max.
CLIMATIC : Temperature range -55 °C up to 125°C
MARKING : Amphenol...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 717 SD D 50 P C309



UNLESS OTHERWISE SPECIFIED			
TOLERANCES		APPROVAL	DATE
METRIC	DRAWN	Issue pending	07/11/07
U.S.	CHECKED	Release pending	07/11/07
X +/-			
XX +/-			
XX +/-			
FRACTIONS +/-			
ANGLES +/-			
2"			
FOR MATERIALS AND FINISHES			
SEE NOTES			
REMOVE SHARP EDGES		ANGLE OF PROJECTION	
U.S.	INCHES		
METRIC	MM		
TITLE			
Stamped and Formed connector, SD series			
SIZE	DRAWING NO.	SCALE	REV.
A4	C L717SDD50PC309	NONE	A
SHEET 1 OF 1			

