



Order Code	H (mm)	ØID (mm)	ØID closed (mm)
520 001 000	17.8	5.1	4.0
520 002 000	16.5	5.6	5.0
520 003 000	23.8	8.3	7.3
520 004 000	28.0	11.5	10.0
520 005 000	32.5	13.2	11.5
520 006 000	30.4	15.4	13.8
520 007 000	35.0	18.8	17.2
520 008 000	42.0	22.0	19.5
520 009 000	41.4	25.8	24.2
520 010 000	55.5	29.0	26.8

Operating Temperature: -30°C up to +85°C  
 Flammability according to: UL94 V-2

				Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions	CREATED DaF	CHECKED SKI	GENERAL TOLERANCE DIN ISO 2768-1m	PROJECTION METHOD		SIZE A4
				Max-Eyth-Str. 1 74638 Waldenburg Germany com. +49 79 42 945 - 0	DESCRIPTION <b>AsCHTW Twister for cables</b>			TECHNICAL REFERENCE	MATERIAL Nylon66, natural	
				www.we-online.de eiSos@we-online.de	SIZE xxx xxx xxx	WEIGHT	STATUS Released	DATE 2016-08-22	BUSINESS UNIT eiCan	PAGE 1 / 1
REV.	FILE	DATE	BY		ORDER CODE 520 0xx 000					



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc.. Würth Elektronik eiSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.