REVISIONS

NAME:

Α4

CAGE CODE DRAWING NO

U5792

□P43735

SCALE

APPLICATION SPEC:

**CUSTOMER DRAWING** 

WEIGHT:

MICRO BAND TERMINATION MICRO MINIATURE BACKSHELL

2:1

SHEET

RESTRICTED TO

AB

SCALE


2:1


SHEET

2 <sup>OF</sup>

AB

**CUSTOMER DRAWING** 





SCALE

SHEET

1.5:1

4 DF

AB

**CUSTOMER DRAWING** 

# COPYRIGHT 20 BY

# REVISIONS


# **AVAILABLE ENTRY SIZES**


	7 (17 (IE) (BEE EI (III (I OIE EO										
SHELL	CONNECTOR	U - TOP ENTRY		F - 45° END ENTRY		E - 90° END ENTRY		J - 45° SIDE ENTRY		S - 90° SIDE ENTRY	
SIZE	REF.	CIRCULAR	ELLIPTICAL	CIRCULAR	ELLIPTICAL	CIRCULAR	ELLIPTICAL	CIRCULAR	ELLIPTICAL	CIRCULAR	ELLIPTICAL
Α	09	02 - 04	NA	02 - 04	NA	02 - 04	NA	02 - 04	NA	02 - 04	NA
В	15	02 - 04	05	02 - 04	05	02 - 04	05	02 - 04	05	02 - 04	05
С	21	02 - 04	05 - 06	02 - 04	05 - 06	02 - 04	05 - 06	02 - 04	05 - 06	02 - 04	05 - 06
D	25	02 - 04	05 - 06	02 - 04	05 - 06	02 - 04	05 - 06	02 - 04	05 - 06	02 - 04	05 - 06
Е	31	02 - 04	05 - 07	02 - 04	05 - 07	02 - 04	05 - 07	02 - 04	05 - 07	02 - 04	05 - 07
F	37	02 - 04	05 - 08	02 - 04	05 - 08	02 - 04	05 - 08	02 - 04	05 - 08	02 - 04	05 - 08
G	51	02 - 05	06 - 08	02 - 05	06 - 08	02 - 05	06 - 08	02 - 05	06 - 08	02 - 05	06 - 08
Н	100	02 - 05	06 - 11	02 - 05	06 - 11	02 - 05	06 - 11	02 - 05	06 - 11	02 - 05	06 - 11

# CIRCULAR ENTRY

# **ENTRY SIZE**

# **ELLIPTICAL ENTRY**





## ENTRY SIZE TABLE 1 - CIRCULAR ENTRY ONLY

ENTRY SIZE (CIRCULAR)	DIA Z MIN	U - TOP ENTRY MINIMUM MAIN BODY	F - 45° END ENTRY MINIMUM MAIN BODY HEIGHT IN mm		E - 90° EN MINIMUM N HEIGHT	MAIN BODY	J - 45° SIE MINIMUM N HEIGHT	MAIN BODY	S - 90° SIDE ENTRY MINIMUM MAIN BODY HEIGHT IN mm		
(CIRCULAR)		HEIGHT IN mm	STANDARD FLANGE	THIN FLANGE	STANDARD FLANGE	THIN FLANGE	STANDARD FLANGE	THIN FLANGE	STANDARD FLANGE	THIN FLANGE	
02	3,18	15,0	25,0	20,0	25,0	20,0	20,0	20,0	20,0	20,0	
03	4,77	15,0	25,0	20,0	30,0	20,0	20,0	20,0	20,0	20,0	
04	6,35	15,0	25,0	20,0	30,0	25,0	20,0	20,0	20,0	20,0	
05	7,93	15,0	30,0	20,0	30,0	25,0	20,0	20,0	20,0	20,0	


# ENTRY SIZE TABLE 2 - ELLIPTICAL ENTRY ONLY

ENTRY SIZE (ELLIPTICAL)	X MIN	N Y MIN	U - TOP ENTRY MINIMUM MAIN BODY HEIGHT IN mm	F - 45° EN MINIMUM A HEIGHT	MAIN BODY	E - 90° EN MINIMUM N HEIGHT	MAIN BODY	J - 45° SIE MINIMUM N HEIGHT	MAIN BODY	S - 90° SIDE ENTRY MINIMUM MAIN BODY HEIGHT IN mm		
(LLLII IICAL)				STANDARD FLANGE	THIN FLANGE	STANDARD FLANGE	THIN FLANGE	STANDARD FLANGE	THIN FLANGE	STANDARD FLANGE	THIN FLANGE	
05	10,70	6,00	15,0	30,0	25,0	35,0	25,0	20,0	20,0	20,0	20,0	
06	15,00	6,00	15,0	30,0	25,0	40,0	30,0	20,0	20,0	20,0	20,0	
07	20,00	6,00	15,0	35,0	30,0	45,0	35,0	20,0	20,0	20,0	20,0	
08	25,00	6,00	15,0	40,0	35,0	50,0	40,0	20,0	20,0	20,0	20,0	
08*	23,50	6,50	15,0	40,0	30,0	50,0	40,0	20,0	20,0	20,0	20,0	
09	25,00	8,00	15,0	40,0	30,0	50,0	40,0	20,0	20,0	20,0	20,0	
10	31,00	8,00	15,0	45,0	35,0	55,0	45,0	20,0	20,0	20,0	20,0	
11	36,00	8,00	15,0	45,0	45,0	60,0	50,0	20,0	20,0	20,0	20,0	


## \* - ENTRY SIZE DIMENSIONS APPLY TO SHELL SIZES G AND H ONLY

DIMENSIONS: MILLIMETERS	DWN: D. WRIGLEY	05/08/2019	MATERIAL: FINISH:
TOLERANCES UNLESS	CHK: R. STYLES	13/08/2019	TE Connectivity
OTHERWISE SPECIFIED:	APVD: M. PAUL	05/08/2019	PART NUMBER: MBMMD SERIES
GENERAL TOL LINEAR ±0,25MM ANGULAR ±1°	PRODUCT SPEC:		NAME:  MICRO BAND TERMINATION MICRO MINIATURE BACKSHELL
	APPLICATION SPEC:		SIZE CAGE CODE DRAWING NO RESTRICTED TO
	WEIGHT:		A4 U5792 C-P43735
¥ —	CUSTOMER DRA	WING	SCALE 1.5:1 SHEET 5 DF 6 REV AB


HARDWARE OPTION CODE: S SLOTTED HEAD JACKSCREW RETAINED WITH 'OVER-END' CLIP MATERIAL: STAINLESS STEEL, PASSIVATE FINISH NOT RECOMMENDED FOR USE WITH ENTRY POSITIONS F AND E



HARDWARE OPTION CODE: H HEX DRIVE SOCKET HEAD JACKSCREW RETAINED WITH 'OVER-END' CLIP MATERIAL: STAINLESS STEEL, PASSIVATE FINISH



HARDWARE OPTION CODE: E EXTENDED SLOTTED HEAD JACKSCREW RETAINED WITH 'OVER-END' CLIP MATERIAL: STAINLESS STEEL, PASSIVATE FINISH NOT AVAILABLE FOR ENTRY POSITIONS E AND F



HARDWARE OPTION CODE: F FEMALE THREAD JACKPOST MATERIAL: STAINLESS STEEL, PASSIVATE FINISH

> HARDWARE OPTION CODE: 0 (ZERO) BACKSHELL SUPPLIED WITHOUT HARDWARE TO BE USED WITH ALL THIN FLANGE BACKSHELL OPTIONS

+	2										
DIMENSIONS: MILLIMETERS  TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN: D. WRIGLEY 05/08/2019		MATERIA	AL:		FINISH:	FINISH:			
		CHK: R. STYLES	13/08/2019			<b>三</b> 7	<b>E</b> TE	Conne	ctivit	У	
		APVD: M. PAUL	05/08/2019	PART NUMBER:			MBMMD SERIES				
GENERAL TOL Linear ±0,25mm angular ±1°	GENERAL TOL	PRODUCT SPEC:	NAME:								
	ANGULAR ±1°	_			MICRO BA	BAND TERMINATION MICRO MINIATURE BAC					SHELL
		APPLICATION SPEC:									
		-		SIZE	CAGE CODE	DRAWING N	10			REST	RICTED TO
		WEIGHT:		Α4	U5792	C-P4	3735				
		CUSTOMER DRA	WING				SCALE 1:1	SHEET	6 <sup>OF</sup>	6	<sup>RE∨</sup> AB