


ST-605
OVERMOLDED 5 PIN FEMALE TINI-QG

CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
INSULATOR - NATURAL (BROWN) THERMOPLASTIC
SHELL - COPPER ALLOY, NICKEL PLATED
OVERMOLD - BLACK THERMOPLASTIC.


Ø 0.190
[4.83]
5 CONDUCTOR
FOIL SHIELD
WITH DRAIN WIRE
BLACK PVC

STRIP & TIN

WIRING CHART	
ST-605	WIRE COLOR
PIN 1	BLACK
PIN 2	WHITE
PIN 3	RED
PIN 4	GREEN
PIN 5	BROWN
SHELL	SHIELD/ DRAINWIRE



ST-605
FRONT MATING VIEW



CUSTOMER DRAWING

NOTES:
1. THIS PRODUCT IS RoHS COMPLIANT.

REV	ECO NUMBER	DATE	BY	APVD
A	28310	08/25/20	PC	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED
1. ALL DIMENSIONS IN INCHES [mm]
- TWO PLACE DECIMALS ±0.02 [0.5]
- THREE PLACE DECIMALS ±0.005 [0.13]
DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON *				SCALE 1.5:1					
DATE DRAWN	BY	CHKD	APVD	Switchcraft®					
7/28/20	AB	AB	TJK	SHEET 1 OF 1					
			7/28/20	8/10/20		PART No. 605HJ__184X			
NAME CABLE ASSEMBLY, 5 PIN FEMALE TINI QG TO S & T, RoHS								REV A	