


ST-604
OVERMOLDED 4 PIN FEMALE TINI-QG

CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
INSULATOR - NATURAL (BROWN) THERMOPLASTIC
SHELL - COPPER ALLOY, NICKEL PLATED
OVERMOLD - BLACK THERMOPLASTIC.


ST-604
OVERMOLDED 4 PIN FEMALE TINI-QG

CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
INSULATOR - NATURAL (BROWN) THERMOPLASTIC
SHELL - COPPER ALLOY, NICKEL PLATED
OVERMOLD - BLACK THERMOPLASTIC.

WIRING CHART STRAIGHT THRU WIRING		
ST-604	WIRE COLOR	ST-604
PIN 1	BLACK	PIN 1
PIN 2	WHITE	PIN 2
PIN 3	RED	PIN 3
PIN 4	GREEN	PIN 4
SHELL	SHIELD/ DRAINWIRE	SHELL



ST-604
FRONT MATING VIEW
BOTH ENDS



NOTES:

- 1. THIS PRODUCT IS RoHS COMPLIANT

CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.					
					SIZE	WIDTH	MULT	LBS/M	TEMPER	
					FINISH SPEC No.			MATERIAL SPEC No.		
					FIRST USED ON		SCALE 1.5:1			
A	28310	08/25/20	PC	TJK	DATE DRAWN 7/28/20	BY AB	CHKD AB 7/28/20	APVD TJK 8/10/20	Switchcraft®	
REVISIONS					NAME: CABLE ASSEMBLY, DOUBLE ENDED 4 PIN FEMALE TINI QG, RoHS					PART No. 604HH__604X
					DO NOT SCALE DRAWING					