
THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

| REVISION |             |      |          |  |  |  |
|----------|-------------|------|----------|--|--|--|
| REV.     | DESCRIPTION | DATE | APPROVED |  |  |  |
|          |             |      |          |  |  |  |
|          |             |      |          |  |  |  |
|          |             |      |          |  |  |  |



## **CONTROLLED**

## NOTES:

- 1. CORDAGE: H03VVH2-F, 2x0.75mm, UNSHIELDED, CEE COLOR CODE, TEMP. RATING 70°C, RATING: 250V 2.5A, JACKET COLOR: BLACK
- 2. PLUG: CEE7/XVI
- 3. CONNECTOR: ROJ 50mm, STRIP 5mm
- 4. APPROVALS: GERMANY, SWITZERLAND, DENMARK, NORWAY, FINLAND, FRANCE, BELGIUM, ITALY, NETHERLANDS, SWEDEN, AUSTRIA
- 5. ROHS COMPLIANT

| Dim<br>range | Tolerance<br>+/- | Qualtek Electronics Corp.  PPC DIVISION |                |                   |  |
|--------------|------------------|---|----------------|-------------------|--|
| (mm)         | (mm)             | Part Number:                            | 361002-01      | RoHS<br>Compliant |  |
| 0-1          | 0.15             | Description: POWER CORD                 |                |                   |  |
| 1-6          | 0.20             |   |                |                   |  |
| 6-18         | 0.30             |   | LINUT          |                   |  |
| 18-50        | 0.50             |   | UNIT: mm       |                   |  |
| 50-120       | 0.70             | Drawn / Date                            | Checked / Date | Approved / Date   |  |
| 120-250      | 0.90             | R.Nuti 06-16-08                         |                | 08 JJH / 06-16-08 |  |
| 250-500      | 1.20             | 06-16-08                                | 00-10-08       | 33117 00-10-08    |  |