






A1	HARD TRAY	WITH/BLACK	2357739-5
	TAPE & REEL	WITH/WHITE	2357739-3
	HARD TRAY	WITH/WHITE	2357739-2
	HARD TRAY	WITHOUT	2357739-1
	PACKAGE	CAP	P/N



SECTION G-G
SCALE 10:1
(GROUND CONTACTS)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC 108-32658 APPLICATION SPEC 114-115003 WEIGHT - CUSTOMER DRAWING		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.05 4 PLC ±0.0250 ANGLES ±3° FINISH -		NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT SIZE A2 CAGE CODE 00779 DRAWING NO C-2357739 RESTRICTED TO -	
MATERIAL - SEE NOTE 1		MATERIAL - SEE NOTE 2		SCALE 1:1 SHEET OF 5 REV A1	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



REFERENCE P.C. BOARD LAYOUT



G: Ground

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 11JUN2019	TE Connectivity		
DIMENSIONS: mm		CHK HOPE LU 10OCT2019			
		APVD HOPE LU 10OCT2019	NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT		
		PRODUCT SPEC 108-32658			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-115003	SIZE A200779	CAGE CODE C-2357739	RESTRICTED TO -
MATERIAL -		WEIGHT -			
SEE NOTE 1		SEE NOTE 2	CUSTOMER DRAWING		
			SCALE 1:1	SHEET 2 OF 5	REV A1


WITHOUT PICK UP CAP
2357739-1

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




SECT. D-D
(SCALE 2:1)
(CONNECTOR NOT SECTION)




DETAIL C
(SCALE 2:1)



E-E
(SCALE 2:1)




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC 108-32658 APPLICATION SPEC 114-115003 WEIGHT -	11JUN2019 10OCT2019 10OCT2019	TE TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.05 4 PLC ±0.0250 ANGLES ±3°	MATERIAL -	SEE NOTE 1	NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT	RESTRICTED TO -
SEE NOTE 2		CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779
SEE NOTE 2		SCALE 1:1		DRAWING NO. C-2357739	SHEET 3 OF 5
SEE NOTE 2		REV A1			




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

WITH PICK UP CAP
2357739-2 &-5



DETAIL E
(SCALE 4:1)






SECT. D-D
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC 108-32658 APPLICATION SPEC 114-115003 WEIGHT -			11JUN2019 10OCT2019 10OCT2019			TE Connectivity		
DIMENSIONS: mm			TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.05 4 PLC ±0.0250 ANGLES ±3° FINISH			NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT			SIZE A2		
MATERIAL -			SEE NOTE 1			CAGE CODE 00779			DRAWING NO C-2357739		
SEE NOTE 2			CUSTOMER DRAWING			SCALE 1:1			SHEET 4 OF 5		
									REV A1		

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


DIRECTION OFF TOP OF REEL

REEL WITH PICK UP CAP
2357739-3




(4.25)

CONNECTOR DETAIL



SEE DETAIL F

WEEDING THE COVER TAPE
AROUND THE OUTER
PERIPHERY IN
A TURN.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC 108-32658 APPLICATION SPEC 114-115003 WEIGHT -	11JUN2019 10OCT2019 10OCT2019	TE TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 1 PLC ± 0.3 2 PLC ± 0.15 3 PLC ± 0.05 4 PLC ± 0.0250 ANGLES $\pm 3^\circ$ FINISH	SEE NOTE 1	SEE NOTE 2	NAME 4H RECEPTACLE ASSY 220POS FH 0.5 BTB 16Gbps WITH G-CONTACT	
MATERIAL -	SEE NOTE 1	SEE NOTE 2	CUSTOMER DRAWING	SIZE A2	CAGE CODE 00779
SCALE 1:1		SHEET 5 OF 5		REV A1	