





P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FORMAL RELEASE	13OCT2020	A.L	H.L



2369315-1
P/N





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Art Lin	24FEB2020	 TE Connectivity							
DIMENSIONS: mm		CHK HOPE LU	26FEB2020	NAME 4H RECEPTACLE ASSY 440POS FH 0.5 BTB 16Gbps FH 0.5MM BTB 16Gbps							
		APVD HOPE LU	26FEB2020								
MATERIAL -	FINISH -	PRODUCT SPEC 108-32658						SIZE A3	CAGE CODE 00779	DRAWING NO C-2369315	RESTRICTED TO -
		APPLICATION SPEC 114-115003									
SEE NOTE 1		SEE NOTE 2		CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 4	REV A		

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Art Lin 24FEB2020	 TE Connectivity				
DIMENSIONS: mm		CHK HOPE LU 26FEB2020	NAME 4H RECEPTACLE ASSY 440POS FH 0.5 BTB 16Gbps FH 0.5MM BTB 16Gbps				
		APVD HOPE LU 26FEB2020					
		PRODUCT SPEC 108-32658					
		APPLICATION SPEC 114-115003					
MATERIAL -		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2369315	RESTRICTED TO -	
SEE NOTE 1		CUSTOMER DRAWING			SCALE 1:1	SHEET 2 OF 4	REV A
SEE NOTE 2							


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



0.10
ALL CONTACTS




SECTION G-G
SCALE 8:1
(GROUND CONTACTS)




NOTES:


- MATERIAL
HOUSING : HIGH TEMP THERMO PLASTIC UL94V-0
CONTACT : COPPER ALLOY
SOLDER PEG : COPPER ALLOY
- FINISH
UNDERPLATED : 1.27µm MIN. NICKEL ALL OVER
CONTACT MATING AREA : MEETS THE PERFORMANCE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-32658.
SOLDER AREA : GOLD FLASH
- CAP COLOR IS BLACK.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Art Lin	24FEB2020	 TE Connectivity	
		CHK HOPE LU	26FEB2020		
		APVD HOPE LU	26FEB2020	NAME 4H RECEPTACLE ASSY 440POS FH 0.5 BTB 16Gbps FH 0.5MM BTB 16Gbps	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-32658	
		0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.050 4 PLC ±0.0250 ANGLES ±3		APPLICATION SPEC 114-115003	
		MATERIAL -		WEIGHT -	
SEE NOTE 1		SEE NOTE 2		CUSTOMER DRAWING	
				SIZE A3	CAGE CODE 00779
				DRAWING NO C-2369315	RESTRICTED TO -
				SCALE 1:1	SHEET 3 OF 4
				REV A	

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SCALE 4:1
REFERENCE P.C. BOARD LAYOUT
G:Ground

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Art Lin 24FEB2020	 TE Connectivity				
DIMENSIONS: mm		CHK HOPE LU 26FEB2020	NAME 4H RECEPTACLE ASSY 440POS FH 0.5 BTB 16Gbps FH 0.5MM BTB 16Gbps				
		APVD HOPE LU 26FEB2020					
		PRODUCT SPEC 108-32658					
		APPLICATION SPEC 114-115003					
MATERIAL - SEE NOTE 1		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2369315	RESTRICTED TO -	
FINISH - SEE NOTE 2		CUSTOMER DRAWING			SCALE 1:1	SHEET 4 OF 4	REV A