






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FORMAL RELEASE	13OCT2020	A.L	H.L
	A1	ECN-21-104438:CORRECT A TYPO	21MAY2021	A.L	H.L
	A2	REVISE AS PER ECN-21-104567	25MAY2021	A.L	H.L




2369317-1
P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Art Lin 24FEB2020		 TE Connectivity													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK Hope Lu 25FEB2020		NAME 8H PLUG ASSY 440POS FH 0.5 BTB 16Gbps											
		0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.050 4 PLC ±0.0250 ANGLES ±3		APVD Hope Lu 25FEB2020													
		PRODUCT SPEC 108-32658		APPLICATION SPEC 114-115003						SIZE A3		CAGE CODE 00779		DRAWING NO C-2369317		RESTRICTED TO -	
		WEIGHT -		CUSTOMER DRAWING						SCALE 1:1		SHEET 1 OF 4		REV A2			
MATERIAL -		FINISH -															
SEE NOTE 1		SEE NOTE 2															



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24FEB2020 Art Lin		TE Connectivity		
		CHK 25FEB2020 Hope Lu				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 8H PLUG ASSY 440POS FH 0.5 BTB 16Gbps		
		0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.050 4 PLC ±0.0250 ANGLES ±3				
MATERIAL -		FINISH -		APVD 25FEB2020 Hope Lu		
				PRODUCT SPEC 108-32658		
				APPLICATION SPEC 114-115003		
				WEIGHT -		
SEE NOTE 1		SEE NOTE 2		CUSTOMER DRAWING		
				SIZE A3		
				CAGE CODE 00779		
				DRAWING NO C=2369317		
				RESTRICTED TO -		
				SCALE 1:1		
				SHEET 2 OF 4		
				REV A2		

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			




NOTES:


- MATERIAL**
HOUSING : HIGH TEMP THERMO PLASTIC UL94V-0
CONTACT : COPPER ALLOY
SOLDER PEG : COPPER ALLOY
GROUND PLATE : COPPER ALLOY
- FINISH**
UNDERPLATED : 1.27µm MIN. NICKEL ALL OVER
CONTACT MATING AREA : MEETS THE PERFORMANCE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-32658.
SOLDER AREA : GOLD FLASH
- CAP COLOR IS BLACK.**

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Art Lin 24FEB2020	 TE Connectivity		
		CHK Hope Lu 25FEB2020			
		APVD Hope Lu 25FEB2020	NAME 8H PLUG ASSY 440POS		
		PRODUCT SPEC 108-32658	FH 0.5 BTB 16Gbps		
		APPLICATION SPEC 114-115003	SIZE A3	CAGE CODE 00779	DRAWING NO C-2369317
		WEIGHT -	RESTRICTED TO -		
CUSTOMER DRAWING		SCALE 1:1	SHEET 3	OF 4	REV A2

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



SCALE 4:1
REFERENCE P.C. BOARD LAYOUT
G:Ground

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Art Lin 24FEB2020	 TE Connectivity				
		CHK Hope Lu 25FEB2020					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Hope Lu 25FEB2020	NAME 8H PLUG ASSY 440POS FH 0.5 BTB 16Gbps				
	0 PLC ±0.5 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.050 4 PLC ±0.0250 ANGLES ±3	PRODUCT SPEC 108-32658					
			APPLICATION SPEC 114-115003	SIZE A3	CAGE CODE 00779	DRAWING NO C-2369317	RESTRICTED TO -
MATERIAL -	FINISH -	WEIGHT -	CUSTOMER DRAWING				
SEE NOTE 1	SEE NOTE 2	SCALE 1:1		SHEET 4 OF 4		REV A2	