


| PART NUMBER     | PACK | HOOD SIZE |
|-----------------|------|-----------|
| 8655DMETIBI3KLF | KIT  | 09        |




NOTES: (FOR EVERY SIZES)  
1- OPERATING TEMPERATURE: -40°C TO +120°C  
2- INDIVIDUAL KITS SEALED IN PLASTIC COVER  
IN UNASSEMBLED FORM.  
BOM AS SHOWN IN TABLE

RoHS INFORMATION:  
- THE LF PRODUCT MEETS EUROPEAN UNION  
DIRECTIVES AND OTHER COUNTRY REGULATIONS  
AS DESCRIBED IN GS+22-009  
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED  
TO A MANUFACTURING SOLDER PROCESS




| ITEM NO. | QTY. | PART DESCRIPTION                     |
|----------|------|--------------------------------------|
| 1        | 1    | DTSLO9-UPPER COVER                   |
| 2        | 1    | DTSLO9-LOWER COVER                   |
| 3        | 3    | M2.5X6 SCREW                         |
| 4        | 1    | CABLE CLAMP                          |
| 5        | 1    | RUBBER GROMMET                       |
| 6        | 1    | PLASTIC INSERT DTSLO9<br>-TOP & SIDE |
| 7        | 2    | UNC4-40x18 JACKSCREW                 |

|               |                     |      |                |                 |                |                 |          |                 |                        |              |
|---------------|---------------------|------|----------------|-----------------|----------------|-----------------|----------|-----------------|------------------------|--------------|
| spec ref      | -                   | dr   | Dipu Joseph    | 2020/09/11      | projection     | mm              | size     | A3              | scale                  | 3:2          |
| tolerance std | ISO 406<br>ISO 1101 | eng  | Detouillon, Da | 2020/11/13      | chr            | -               | ecn no   | -               | rel level              | Released     |
| surface       | linear              | appr | Wollin, Severi | 2020/11/13      | product family | -               | cat. no. | -               | Product - Customer Drw | sheet 1 of 4 |
| ISO 1302      | angular             | 0°   | ±2°            | Amphenol<br>FCi | title          | DSUB METAL HOOD | dwg no   | 8655DMxxIBI3KLF | rev                    | A            |

| PART NUMBER     | PACK | HOOD SIZE |
|-----------------|------|-----------|
| 8655DMATIBI3KLF | KIT  | 15        |








| ITEM NO. | QTY. | PART DESCRIPTION          |
|----------|------|---------------------------|
| 1        | 1    | DTSL15-UPPER COVER        |
| 2        | 1    | DTSL15-LOWER COVER        |
| 3        | 3    | M2.5X6 SCREW              |
| 4        | 1    | CABLE CLAMP               |
| 5        | 1    | RUBBER GROMMET            |
| 6        | 1    | PLASTIC INSERT DTSL 15/37 |
| 7        | 2    | UNC4-40x18 JACKSCREW      |



|               |                     |      |                |                 |                 |          |           |                        |              |          |
|---------------|---------------------|------|----------------|-----------------|-----------------|----------|-----------|------------------------|--------------|----------|
| spec ref      | -                   | dr   | Dipu Joseph    | 2020/09/11      | projection      | mm       | size      | A3                     | scale        | 3:2      |
| tolerance std | ISO 406<br>ISO 1101 | eng  | Detouillon, Da | 2020/11/13      | chr             | -        | ecn no    | -                      | rel level    | Released |
| surface       | linear              | appr | Wollin, Severi | 2020/11/13      | product family  | -        | rel level | Released               | rev          | A        |
| ISO 1302      | angular             | 0°   | ±2°            | Amphenol<br>FCi | DSUB METAL HOOD | cat. no. | -         | Product - Customer Drw | sheet 2 of 4 |          |



| PART NUMBER     | PACK | HOOD SIZE |
|-----------------|------|-----------|
| 8655DMBTIBI3KLF | KIT  | 25        |



| ITEM NO. | QTY. | PART DESCRIPTION          |
|----------|------|---------------------------|
| 1        | 1    | DTSL25-UPPER COVER        |
| 2        | 1    | DTSL25-LOWER COVER        |
| 3        | 4    | M2.5X6 SCREW              |
| 4        | 1    | CABLE CLAMP               |
| 5        | 1    | RUBBER GROMMET            |
| 6        | 1    | PLASTIC INSERT DTSL 15/37 |
| 7        | 2    | UNC4-40x18 JACKSCREW      |

|               |                     |      |                |                 |                 |        |                 |     |                        |              |
|---------------|---------------------|------|----------------|-----------------|-----------------|--------|-----------------|-----|------------------------|--------------|
| spec ref      | -                   | dr   | Dipu Joseph    | 2020/09/11      | projection      | mm     | size            | A3  | scale                  | 1:1          |
| tolerance std | ISO 406<br>ISO 1101 | eng  | Detouillon, Da | 2020/11/13      | chr             | -      | ecn no          | -   | rel level              | Released     |
| surface       | linear              | appr | Wollin, Severi | 2020/11/13      | product family  | -      | cat. no.        | -   | Product - Customer Drw | sheet 3 of 4 |
| ISO 1302      | angular             | 0°   | ±2°            | Amphenol<br>FCi | DSUB METAL HOOD | dwg no | 8655DMxxIBI3KLF | rev | A                      |              |

|                 |      |           |
|-----------------|------|-----------|
| PART NUMBER     | PACK | HOOD SIZE |
| 8655DMCTIBI3KLF | KIT  | 37        |



| ITEM NO. | QTY. | PART DESCRIPTION                               |
|----------|------|------------------------------------------------|
| 1        | 1    | DTSL37-UPPER COVER                             |
| 2        | 1    | DTSL37-LOWER COVER                             |
| 3        | 4    | M2.5X6 SCREW                                   |
| 4        | 1    | CABLE CLAMP                                    |
| 5        | 1    | PLASTIC INSERT DTSL 15-37 TOP & SIDE METALISED |
| 6        | 2    | UNC4-40x18 JACKSCREW                           |
| 7        | 1    | RUBBER GROMMET                                 |

|               |                                        |         |                |                 |                |                 |          |                 |                        |              |
|---------------|----------------------------------------|---------|----------------|-----------------|----------------|-----------------|----------|-----------------|------------------------|--------------|
| spec ref      | -                                      | dr      | Dipu Joseph    | 2020/09/11      | projection     | mm              | size     | A3              | scale                  | 1:1          |
| tolerance std | ISO 406<br>ISO 1101                    | eng     | Detouillon, Da | 2020/11/13      | chr            | -               | ecn no   | -               | rel level              | Released     |
| surface       | ISO 1302                               | appr    | Wollin, Severi | 2020/11/13      | product family | -               | cat. no. | -               | Product - Customer Drw | sheet 4 of 4 |
| linear        | 0.X ±0.3<br>0.XX ±0.10<br>0.XXX ±0.005 | angular | 0° ±2°         | Amphenol<br>FCi | title          | DSUB METAL HOOD | dwg no   | 8655DMxxIBI3KLF | rev                    | A            |