





12CCT RECEPTACLE CONNECTOR



DATE CODE: X XX XX
X- DAY: 1- 7
XX- WEEK: 01 - 52
XX- YEAR: 00 - 99
MACHINE NO. 1

EXAMPLE: 11315 = DAY 1, WEEK 13, YEAR 15
i.e. 23rd OF MARCH 2015

DETAIL A
SCALE 2:1



1. THIS RECEP MATES WITH PLUG ASSEMBLY PN X-2600043-X FOR THE CORRESPONDED KEYING.

2. MATERIAL
HOUSING: NYLON GF30
BACK SEAL: SILICONE RUBBER
BACK COVER: NYLON GF30, BLACK
HEATSHRINK HOUSING: NYLON GF30, BLACK


3 CIRCUIT IDENTIFICATION

4. JACKET RANGE LARGE = $\varnothing$ 2.23mm TO 3.68mm (SEAL COLOUR: LIGHT BLUE)
JACKET RANGE SMALL = $\varnothing$ 1.20mm TO 3.05mm (SEAL COLOUR: BURNT ORANGE)




5. SEE SHEET 3 FOR FINAL PART NUMBER DESIGNATION


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	20JUN2020	J.S	I.Y
	A1	ECR-20-010349	26JUL2020	J.G	I.Y



12CCT RECEPTACLE CONNECTOR WITH HEATSHRINK
HOUSING ULTRASONICALLY WELDED IN PLACE




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.Gu 26JUN2020	 TE Connectivity		
		CHK E.Jiang 26JUN2020			
		APVD I.Yin 26JUN2020			
		PRODUCT SPEC 108-160026			
DIMENSIONS: mm		APPLICATION SPEC 114-160017	NAME 12CCT DT-XT RECEPTACLE CONNECTOR		
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2600042
MATERIAL -		FINISH -	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 3	REV A1


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			


KEYING OPTION A








KEYING OPTION B




KEYING OPTION C




KEYING OPTION D




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.Gu 26JUN2020		TE Connectivity					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 12CCT DT-XT RECEPTACLE CONNECTOR					
		0 PLC ±		PRODUCT SPEC					
		1 PLC ±		108-160026					
		2 PLC ±		APPLICATION SPEC					
		3 PLC ±		114-160017					
4 PLC ±		APVD L.Yin 26JUN2020		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
ANGLES ±		WEIGHT -		A 3		00779	©=2600042	-	
MATERIAL - -		FINISH - -		CUSTOMER DRAWING					
					SCALE 1:1		SHEET 2 OF 3		REV A1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



2- -0	934446647	-	21.48		-	-	-	-	1	-	1	1	1
1- -9	934446633	-	21.48		-	-	-	1	-	-	1	1	1
1- -8	934446621	-	21.48		-	-	1	-	-	-	1	1	1
1- -7	934446611	-	21.48		-	1	-	-	-	-	1	1	1
1- -6	934446612	-	21.48		1	-	-	-	-		1	1	1
1- -5	934446547	-	21.48		-	-	-	-	1	1	-	1	1
1- -4	934446533	-	21.48		-	-	-	1	-	1	-	1	1
1- -3	934446521	-	21.48		-	-	1	-	-	1	-	1	1
1- -2	934446511	-	21.48		-	1	-	-	-	1	-	1	1
1- -1	934446512	-	21.48		1	-	-	-	-	1	-	1	1
1- -0	934446247	-	18.53		-	-	-	-	1	-	1	1	-
-9	934446233	-	18.53		-	-	-	1	-	-	1	1	-
-8	934446221	-	18.53		-	-	1	-	-	-	1	1	-
-7	934446211	-	18.53		-	1	-	-	-	-	1	1	-
-6	934446212	-	18.53		1	-	-	-	-		1	1	-
-5	934446147	-	18.53		-	-	-	-	1	1	-	1	-
-4	934446133	-	18.53		-	-	-	1	-	1	-	1	-
-3	934446121	-	18.53		-	-	1	-	-	1	-	1	-
-2	934446111	-	18.53		-	1	-	-	-	1	-	1	-
-1	934446112	-	18.53		1	-	-	-	-	1	-	1	-
TE PN	ALIAS PN	REVISION OF EACH ASSY NO.	WEIGHT OF EACH ASSY(g)	KEYING	A	A	B	C	D	-	-	-	-
				COLOR	GERY	BLACK	BLACK	GREEN	BROWN	BURNT ORANGE	LIGHT BLUE	BLACK	BLACK
				MATERIAL	NYLON GF30	NYLON GF30	NYLON GF30	NYLON GF30	NYLON GF30	SILICONE RUBBER	SILICONE RUBBER	NYLON GF30	NYLON GF30
				DESCRIPT ION	RECEPTACLE HOUSING					BACK SEAL SMALL	BACK SEAL LARGE	BACK COVER	HEATSHRINK HOUSING
				ITEM NO	1					2		3	4

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J.Gu 26JUN2020	 TE Connectivity							
				CHK E.Jiang 26JUN2020								
				APVD L.Yin 26JUN2020								
				PRODUCT SPEC 108-160026								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-160017	NAME 12CCT DT-XT RECEPTACLE CONNECTOR							
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		WEIGHT -								
MATERIAL -		FINISH -		CUSTOMER DRAWING				SCALE 1:1	SHEET 3 OF 3		REV A1	