

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2174811204

Status:


Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Mini-Fit Sr. Female-to-Pigtail, Gold (Au) Plating, 300.00mm Length, 12 AWG, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	217481
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Sr. Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Mini-Fit Sr.
UPC	195842122246
Physical	
Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	14.036/g
Number of Rows	1
Packaging Type	Bag
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	6.60mm max.
Wire Size AWG	12
Wire/Cable Type	UL 10669
Electrical	
Current - Maximum per Contact	50.0A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2174811202-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

217481 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION