

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2177921121](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead Squba 1.8 Male-to-Squba 1.8 Male, Tin (Sn) Plating, 75.00mm Length, 22 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series [217792](#)
Assembly Configuration Pre-crimped Lead Only
Connector to Connector Squba Crimp Terminals
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name Squba
UPC 195842124370

Physical

Cable Length 75.00mm
Circuits (Loaded) 1
Color - Resin Black
Gender Male-Male
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin PVC
Net Weight 0.580/g
Number of Rows 1
Packaging Type Bag
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 0.95mm-1.40mm
Wire Size AWG 22
Wire/Cable Type UL 10002

Electrical

Current - Maximum per Contact 6.0A
Voltage - Maximum 125V

Material Info

Reference - Drawing Numbers

Sales Drawing 2177921121-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[217792](#) Series