




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	NEW RELEASE	24-JAN-11	PT	St.P
	B1	REVISED PER ECR-20-015376	28OCT2020	SR	AP

FOR FURTHER INFORMATION SEE DATA SHEET FOR
HIGH POWER CAPACITOR DISCHARGE RESISTORS YP SERIES



DIMENSIONS

	A ±1mm	B max.	C ±1mm	D ±1mm	E ±1mm
YP8	22.2	40	15	21	9.5
YP10	31.8	50	15	21	9.5

© 2020 TE Connectivity. All Rights Reserved.

DIMENSIONS:

mm

DWN T.PARUSURAM 24-JAN-2011

MATERIAL

FINISH

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

CHK ALLAN.P 24-JAN-2011

APVD STEPHEN.P 24-JAN-2011

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME HIGH POWER CAPACITOR DISCHARGE
RESISTORS YP SERIES

SIZE CAGE CODE DRAWING NO


A 4 00779 C-1630184

RESTRICTED TO

SCALE 3:1

SHEET 1 OF 2

REV B1




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

PART SCHEDULE

TCPN	PART DESCRIPTION	ALIAS	TYPE	PART STATUS	COMMENT
1630184-1	YP10 10K 5%	YP1010KJ	YP10	Production	Standard
1630184-2	YP10 10K 5%	1630184-2	YP10	Discontinued	Use 1630184-1
1630184-3	YP10 18K 5%	YP1018KJ	YP10	Production	Standard
1630184-4	YP10 18K 5%	1630184-4	YP10	Discontinued	Use 1630184-3
1630184-5	YP10 27K 5%	YP1027KJ	YP10	Production	Standard
1630184-6	YP10 27K 5%	1630184-6	YP10	Discontinued	Use 1630184-5
1630184-7	YP10 2K0 5%	YP102K0J	YP10	Production	Standard
1630184-8	YP10 2K0 5%	1630184-8	YP10	Discontinued	Use 1630184-7
1630184-9	YP10 47K 5%	YP1047KJ	YP10	Production	Standard
1-1630184-0	YP10 47K 5%	1-1630184-0	YP10	Superseded	Use 1630184-9
1-1630184-1	YP10 33K 5%	YP1033KJ	YP10	Discontinued	Standard
1-1630184-2	YP8 18K 5%	YP818KJ	YP8	Production	Standard
1-1630184-3	YP10 10K 5%	YP1010KJV	YP10	Production	Special - MOQ 2000

© 2020 TE Connectivity. All Rights Reserved.

DIMENSIONS:		DWN T.PARUSURAM	24-JAN-2011	MATERIAL		FINISH	
mm		CHK ALLAN.P	24-JAN-2011	 TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD STEPHEN.P	24-JAN-2011				
0 PLC	±0.2	PRODUCT SPEC		NAME HIGH POWER CAPACITOR DISCHARGE RESISTORS YP SERIES			
1 PLC	±0.1	-					
2 PLC	±	APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
3 PLC	±	-		A 4	00779	©-1630184	
4 PLC	±	WEIGHT					
ANGLES	±5°	-					
		CUSTOMER DRAWING		SCALE	3:1	SHEET	2 OF 2
						REV	B1