
# **PRODUCT DATA DRAWING**

REVISION HISTORY				
REV	DESCRIPTION	DATE	APPROVED	
-	NRN 45908	05/21		
			SEE PDM	



## **MATERIAL:**

2.4mm STR. M (1611-60025) **CONNECTORS:** 

SILICONE RUBBER 80A (220-70-145) STRAINRELIEF BOOT:

STANDARD .047 FLEXTRA (200-70-214) CABLE:

PERFORMANCE:

IMPEDANCE: 50 OHMS FREQ. RANGE:

DC TO 50.0 GHz.

MATERIAL:	SEE NOTES	
FINISH:	SEE NOTES	

SURFACE AREA: N/A

#### PROPRIETARY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

### DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'

DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE	<b>PROJECTIO</b>
<b>(</b>	<del></del>

#### UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING
3) BREAK CORNERS & EDGES 005 R. MAX.
4) CHAM. 15T & LAST THREADS.
5) SURFACE ROUGHNESS 63-MIL-STD-10.
6) DIA. 'S ON COMMON CENTERS TO BE CONCENTRIC
WITHIN .005 T.I.R.
7) REMOVE ALL BURRS

DRAWN:	JPM 05/14/21
CHECKED:	SEE PDM
APPROVED:	SEE PDM



2.4mm STR. M TO 2.4mm STR. M ON STD. FLEXTRA CABLE

-	SIZE <b>B</b>	DWG. NO.	7016-0	0121
	S	CALE: 4:1		SHEET 1

SHEET 1 OF 1