
Pro-SIGNAL	PART NO.		REVISIONS							
		ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	ABI-006-RC	-	А	RELEASED	Jagan	06/04/09	Veena	06/04/09	Farnell	20/04/09



## Features:

- Colour : Black.
- Housing material : ABS.
- Built-in oscillating circuit.
- Lead wire : 28 AWG.

Tolerance: ±0.5

Dimensions : Millimetres

All data at 25°C unless otherwise specified.

Specifications	ABI-006-RC Piezo Indicator
Rated Voltage	12V dc
Operating Voltage	3 to 16V dc
Rated Current at Rated Voltage	8mA
Sound Output at 30cm, at Rated Voltage	≥90dB
Resonant Frequency at Rated Voltage	3700 ±500Hz
Operating Temperature	-20 to +60°C
Storage Temperature	-30 to +80°C
Weight	5g

## Part Number Table

Description	Part Number
Piezo Buzzer, 12V dc, Lead	s ABI-006-RC

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk

believed to be accurate but the Group assumes no responsibility for its accuracy of the completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or or	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:				
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Jagan	06/04/09		ABI-006-RC - Piezo Buzzer			
		CHECKED BY:	DATE:	SIZE DWG NO.		ELECTRONIC FILE	REV A	
		Veena	06/04/09	А	e	66691 DWG		
		APPROVED BY:	DATE:					
		Farnell	20/04/09	SCALE: NTS	U.O.M.: mm	SHEET: 1 O	F 1	