

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** 0152660319

**Status:** Active

**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Tin (Sn) Plating, 30 Circuits

**Documents:**

|                                                              |                                                      |
|--------------------------------------------------------------|------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Datasheet (PDF)</a>                      |
| <a href="#">Product Specification PS-15266-001-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

**General**

|                         |                                                           |
|-------------------------|-----------------------------------------------------------|
| Product Family          | Cable                                                     |
| Series                  | 15266                                                     |
| Comments                | Contacts on the same side, Type A                         |
| Crimp Quality Equipment | Yes                                                       |
| Overview                | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers |
| Product Name            | Premo-Flex FFC Jumper                                     |
| UPC                     | 884982437043                                              |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Length                  | 76.00mm         |
| Circuits (Loaded)             | 30              |
| Contact Layout Type           | A (same side)   |
| Material - Plating Mating     | Tin             |
| Net Weight                    | 0.765/g         |
| Packaging Type                | Bag             |
| Pitch - Mating Interface      | 0.50mm          |
| Temperature Range - Operating | -40° to +105°C  |
| Wire Size AWG                 | N/A             |
| Wire/Cable Type               | Flat Flex Cable |

**Electrical**

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 0.5A   |
| Voltage - Maximum             | 60V AC |

**Material Info**

**Reference - Drawing Numbers**

|                       |                  |
|-----------------------|------------------|
| Product Specification | PS-15266-001-001 |
| Sales Drawing         | SD-15266-001-001 |



Series image - Reference only

**EU ELV**

Not Relevant

**EU RoHS**

Compliant

**China RoHS**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

15266 Series

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[524353033](#) , [541043033](#) , [524373033](#) ,  
[541323033](#) , [5019513000](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION