

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0982680265

Status:

Active

Overview:

FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Description:

1.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 152.00mm Cable Length, Tin (Sn) Plating, 20 Circuits



Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-98268-001-001 \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	98268
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	756054777732
Physical	
Cable Length	152.00mm
Circuits (Loaded)	20
Contact Layout Type	A (same side)
Material - Plating Mating	Tin
Net Weight	2.632/g
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable
Electrical	
Current - Maximum per Contact	1.4A
Voltage - Maximum	60V AC
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-98268-001-001
Sales Drawing	SD-98268-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

98268 Series

Mates With

Molex FFC – FPC connector. Be sure to match like plating.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION