





	REVISED	DATE	APP.
①			
②			
③			



US JACK 1
6P6C 3u”



US JACK 2
6P6C 3u”



US JACK1	US JACK2	COLOR
1	1	WHITE
2	2	BLACK
3	3	RED
4	4	GREEN
5	5	YELLOW
6	6	BLUE

UNSIFTED TOLERANCE: ± 0.5

5	WIRE	ø0.95±0.05/26AWG	6	WH,BK,RD,GN,YL,BL	PP/COPPER WIRE		
4	SPRING	ø0.45mm/PLATED 3u”	12		PHOSPHOROUS BRONZE		
3	CRIMP TERMINAL		12		BRASS		
2	INSERT	6 HOLE	2	IVORY	ABS 94HB		
1	HOUSING		1	IVORY	ABS 94HB		
PART	NAME	DESCRIPTION	QTY	COLOR	MATERIAL	VENDER	REMARK

	ISSUE: A	TITLE: US JACK TO JACK			
	SHEET: 1/1	SIZE: A4	CUST:	CUST P/N: TE08638	DWG NO.: ENQ-PR-176-67
	SCALE 1:1	UNIT: MM			
	DRAW: Zh	DATE: 24.02.21'			
	CHECK:	APPROVE:			