


		REVISIONS			
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASE NEW DRAWING	11MAY20	IAN	TOMMY
A2	-	MODIFY PRODUCT NAME	11AUG20	IAN	TOMMY







NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL:


HOUSING: THERMOPLASTIC; BLACK SEAL: SILICONE RUBBER

2. MODIFICATIONS: SMOOTH RING ADAPTER(SRA); REDUCED DIA. WIRE SEAL;

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION).
 - 3.5 MATING CYCLE DURABILITY: 100 CYCLES
 - 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP04-24-16P* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.



CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
12	2.46 mm (.097 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS



SMOOTH RING ADAPTER - BLUE

	AHDP06-24-16SR-SRA			REI	REF:HDP26-24-16SE			
	PART NUMBER				DESCRIPTION	ITEM		
QUANTITY MAT			MAT	ERI	ALS LIST			
	UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows:		ATURES	DATE	Amphonol			
			OAIX.NAI	11AUG20	Amphenol			
2 PL DEC ±0.15 3 PL DEC ±0.08	Fractions ±1/64 Angles ±1°	CHECKED:	ORION.LI	12AUG20	44724 Morley Drive Clinton Township. MI 48036			
3) Note reference	- ∕x	ENGINEER:						
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY.XIE	13AUG20				
		CUSTOMER:			PLUG,SIZE 24,16-PIN,			
			IG IS SUPPLIED N ONLY, DESIGN		RD01 SEAL,SRA,DURAMATE AHDP SERIE	S		
PROCESS SPECIFICATIONS:		SPECIFICATION SHOWN HERITHE AMPHEN OF REPRODUCTION DIMENSIONS	ONS AND PERFO EON ARE THE PI IOL CORPORATI ICTION ARE IMP ARE SUBJECT T	ORMANCE DATA ROPERTY OF ION. NO RIGHTS LIED. ALL	B C- AHDP06-24-16SR-SRA			
NEXT ASS'Y:		MANUFACTU	RING VARIATION	IS.	SCALE: NONE DURAMATE SHEET 1 OF	1		

ATP Series™ - Contact Size 12 Options

Machined Contacts, Sockets & Pins							
Part Number	Size	AWG	Туре				
AT60-204-12141-10	Male Contact - Pin, Nickel-plated	12	10-12	Machined			
AT62-203-12141-10	Female Contact - Socket, Nickel-plated	12	10-12	Machined			
AT60-220-1231	Male Contact - Pin, Gold-plated	12	12-14	Machined			
AT62-210-1231	Female Contact - Socket, Gold-plated	12	12-14	Machined			
AT60-204-12141	Male Contact - Pin, Nickel-plated	12	12-14	Machined			
AT62-203-12141	Female Contact - Socket, Nickel-plated	12	12-14	Machined			

Smaller AWG for	DiagnosticGrade™ Machined Contacts, Sockets & Pins • Smaller AWG for Diagnostic Applications • Gold-plated • Increased Mating Cycles • Cost-effective					
Part Number	Description	Size	AWG	Туре		
65-54749	Male Contact - DiagnosticGrade™, Pin, Gold-plated	12	20	Machined		
AT62-210-1231-1820	Female Contact - DiagnosticGrade™, Socket, Gold-plated	12	20	Machined		

Tooling - Machined Contacts				
Part	Part Number	Description		
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)		
33	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)		

Contact Removal Tools					
Part	Part Number	Description			
refer turbs	ATRT-100	Used for removal of contacts for A Series™ products			
	AT11-337-1205	Contact Removal Tool, Plastic, Size 12			
	A114017	Sealing Plug, Size 12, White			

Stamped & Formed Contacts, Sockets & Pins							
Part Number	Description	Size	AWG	Туре			
AT60-12-0244	Male Contact - Pin, Gold-plated	12	10-12	Stamped & Formed			
AT62-12-0244	Female Contact - Socket, Gold-plated	12	10-12	Stamped & Formed			
AT60-12-0222	Male Contact - Pin, Nickel-plated	12	10-12	Stamped & Formed			
AT62-12-0222	Female Contact - Socket, Nickel-plated	12	10-12	Stamped & Formed			
AT60-12-0144	Male Contact - Pin, Gold-plated	12	12-14	Stamped & Formed			
AT62-12-0144	Female Contact - Socket, Gold-plated	12	12-14	Stamped & Formed			
AT60-12-0166	Male Contact - Pin, Nickel-plated	12	12-14	Stamped & Formed			
AT62-12-0166	Female Contact - Socket, Nickel-plated	12	12-14	Stamped & Formed			

Tooling - Stamped & Formed Contacts				
Part	Part Number	Description		
	MFX-3973	Crimp Die - Size 12 (S&F contacts only)		
	MFX-3985	Crimp Die - Size 12 (S&F contacts only) 10-12AWG -02XX Series		
	ATT-12-00	Hand Crimp Tool - Size 12, 12AWG (S&F contacts only)		

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021