


ITEM	MOLEX PART#	DESCRIPTION	QTY	UOM
A,B	1510340012	Guardian II Rcpt Hsg 6AWG PBT 2Ckt	2	PC
C	1510760012	Guardian II TPA PBT 2Ckt	2	PC
D	468190013	Guardian TERM, 6AWG CRIMP, GOLD	4	PC
E	--	PART IDENTIFICATION LABEL	1	PC

FROM	TO	CABLE PART#	DESCRIPTION	COLOR
A1	B1	--	6AWG,UL 10669,PVC BLACK,105C,600V,VW-1	BLACK
A2	B2			

EXPLODED VIEW OF WIRE HARNESS FOR REFERENCE



PART#	DESCRIPTION	LENGTH (L)
2180560205	2 CKT DISCR GUARDIAN R-R 500MM	500±10
2180560210	2 CKT DISCR GUARDIAN R-R 1M	1000±20
2180560220	2 CKT DISCR GUARDIAN R-R 2M	2000±20

NOTES:
1.CABLE ASSY. TO BE ENSURED FOR CONTINUITY AND POLARITY.
2.CONNECTOR VIEW IS SHOWN FROM MATING SIDE.
3.UL10669 CABLE MEETS OPERATING TEMP. OF 105°C & FLAMMABILITY CLASS OF VW-1.
4.ASSY. TO MEET PS - 151053.
5.PART IDENTIFICATION LABEL TO BE PRINTED AS PER BELOW

P/N : 218056XXXX
MOLEX
BATCH : WK/YR

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
F A = 0 F E = 0 F P = 0		DIMENSION UNITS		SCALE		CURRENT REV DESC: mo lex SEE TABLE PRODUCT CUSTOMER DRAWING									
		mm		NTS											
		GENERAL TOLERANCES (UNLESS SPECIFIED)													
		ANGULAR TOL ± 1.0 °													
		4 PLACES		±											
DIVISIONAL SYMBOLS		3 PLACES		±		EC NO: 685917									
		2 PLACES		± 0.25		DRWN: VSHEELAVANT 2021/11/18									
		1 PLACE		± 0.5		CHK'D: AMV 2021/12/07									
		0 PLACES		±		APPR: AMV 2021/12/07									
		INITIAL REVISION:		DRWN: VSHEELAVANT 2021/02/23											
						APPR: AMV 2021/12/07									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
				A3-SIZE		218056		2180560205		PSD		000		C	
								MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
								SEE TABLE		OTS				1 OF 1	