


ITEM	MOLEX PART#	DESCRIPTION	QTY	UOM
A,B	1510340013	Guardian II Rcpt Hsg 6AWG PBT 3Ckt	2	PC
C	1510760013	Guardian II TPA PBT 3Ckt	2	PC
D	468190013	Guardian TERM, 6AWG CRIMP, GOLD	6	PC
E	--	PART IDENTIFICATION LABEL	1	PC

FROM	TO	CABLE PART#	DESCRIPTION	COLOR
A1	B1	--	6AWG,UL10669,PVC BLACK,105C,600V,VW-1	BLACK
A2	B2			
A3	B3			



PART#	DESCRIPTION	LENGTH (L)
2180560305	3 CKT DISCR GUARDIAN R-R 500MM	500±10
2180560310	3 CKT DISCR GUARDIAN R-R 1M	1000±20
2180560320	3 CKT DISCR GUARDIAN R-R 2M	2000±20

- NOTES:
- 1.CABLE ASSY. TO BE ENSURED FOR CONTINUITY AND POLARITY.
 - 2.CONNECTOR VIEW IS SHOWN FROM MATING SIDE.
 - 3.UL10669 CABLE MEETS OPERATING TEMP. OF 105°C & FLAMMABILITY CLASS OF VW-1.
 - 4.ASSY. TO MEET PS - 151053.
 - 5.PART IDENTIFICATION LABEL TO BE PRINTED AS PER BELOW

P/N : 218056XXXX
MOLEX
BATCH : WK/YR

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
	DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 685917 DRWN: VSHEELAVANT 2021/11/18 CHK'D: AMV 2021/12/07 APPR: AMV 2021/12/07 INITIAL REVISION: DRWN: VSHEELAVANT 2021/02/23 APPR: AMV 2021/12/07												
	mm		NTS														
	GENERAL TOLERANCES (UNLESS SPECIFIED)																
ANGULAR TOL ± 1.0 °										SEE TABLE							
4 PLACES		±															
3 PLACES		±															
2 PLACES		± 0.25															
1 PLACE		± 0.5															
DIVISIONAL SYMBOLS	0 PLACES		±		PRODUCT CUSTOMER DRAWING												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
										2180560305		PSD		000		C	
										MATERIAL NUMBER		CUSTOMER				SHEET NUMBER	
										SEE TABLE		OTS				1 OF 1	