



ITEM	MOLEX PART#	DESCRIPTION	QTY	UOM
A	1510340012	Guardian II Rcpt Hsg 6AWG PBT 2Ckt	1	PC
B	1510760012	Guardian II TPA PBT 2Ckt	1	PC
C	468190013	Guardian TERM, 6AWG CRIMP, GOLD	2	PC
D	--	PART IDENTIFICATION LABEL	1	PC

FROM	TO	CABLE PART#	DESCRIPTION	COLOR
A1	OPEN ENDS	--	6AWG,UL 10669,PVC BLACK,105C,600V,VW-1	BLACK
A2				

EXPLODED VIEW OF WIRE HARNESS FOR REFERENCE



PART#	DESCRIPTION	LENGTH (L)
2180570205	2 CKT DISCR GRDN R-BLUNTCUT 500MM	500±10
2180570210	2 CKT DISCR GRDN R-BLUNTCUT 1M	1000±20
2180570220	2 CKT DISCR GRDN R-BLUNTCUT 2M	2000±20

- NOTES:
- 1.CABLE ASSY. TO BE ENSURED FOR CONTINUITY AND POLARITY.
 - 2.CONNECTOR VIEW IS SHOWN FROM MATING SIDE.
 - 3.UL10669 CABLE MEETS OPERATING TEMP. OF 105°C & FLAMMABILITY CLASS OF VW-1.
 - 4.ASSY. TO MEET PS - 151053.
 - 5.PART IDENTIFICATION LABEL TO BE PRINTED AS PER BELOW

P/N : 218057XXXX
MOLEX
BATCH : WK/YR

FUNCTIONAL SYMBOLS

$\nabla_A = 0$

$\nabla_E = 0$

$\nabla_F = 0$

DIVISIONAL SYMBOLS

DIMENSION UNITS

mm

SCALE

NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± 1.0 °

4 PLACES ±

3 PLACES ±

2 PLACES ± 0.25

1 PLACE ± 0.5

0 PLACES ±

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 685917

DRWN: VSHEELAVANT 2021/11/18

CHK'D: AMV 2021/12/07

APPR: AMV 2021/12/07

INITIAL REVISION:

DRWN: VSHEELAVANT 2021/02/23

APPR: AMV 2021/12/07

THIRD ANGLE PROJECTION

DRAWING

SERIES

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

molex

SEE TABLE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

DOC TYPE

DOC PART

REVISION

A3-SIZE

218057

SEE TABLE

OTS

1 OF 1