



ITEM	MOLEX PART#	DESCRIPTION	QTY	UOM
A	1510340012	Guardian II Rcpt Hsg 6AWG PBT 2Ckt	1	PC
B	1510760012	Guardian II TPA PBT 2Ckt	1	PC
C	468190013	Guardian TERM, 6AWG CRIMP, GOLD	2	PC
D	--	PART IDENTIFICATION LABEL	1	PC

FROM	TO	CABLE PART#	DESCRIPTION	COLOR
A1	OPEN ENDS	--	6AWG,UL 10669,PVC BLACK,105C,600V,VW-1	BLACK
A2				

EXPLODED VIEW OF WIRE HARNESS FOR REFERENCE



PART#	DESCRIPTION	LENGTH (L)
2180570205	2 CKT DISCR GRDN R-BLUNTCUT 500MM	500±10
2180570210	2 CKT DISCR GRDN R-BLUNTCUT 1M	1000±20
2180570220	2 CKT DISCR GRDN R-BLUNTCUT 2M	2000±20

- NOTES:
- 1.CABLE ASSY. TO BE ENSURED FOR CONTINUITY AND POLARITY.
 - 2.CONNECTOR VIEW IS SHOWN FROM MATING SIDE.
 - 3.UL10669 CABLE MEETS OPERATING TEMP. OF 105°C & FLAMMABILITY CLASS OF VW-1.
 - 4.ASSY. TO MEET PS - 151053.
 - 5.PART IDENTIFICATION LABEL TO BE PRINTED AS PER BELOW

P/N : 218057XXXX
MOLEX
BATCH : WK/YR

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
FA= 0 FE= 0 FD= 0 DIVISIONAL SYMBOLS	DIMENSION UNITS			SCALE		CURRENT REV DESC:					molex					
	mm			NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)															
	ANGULAR TOL ± 1.0 °															
	4 PLACES		±								EC NO: 685917 DRWN: VSHEELAVANT 2021/11/18 CHK'D: AMV 2021/12/07 APPR: AMV 2021/12/07					
	3 PLACES		±													
	2 PLACES		± 0.25													
	1 PLACE		± 0.5													
	0 PLACES		±			INITIAL REVISION: DRWN: VSHEELAVANT 2021/02/23 APPR: AMV 2021/12/07					DOCUMENT NUMBER 2180570205		DOC TYPE PSD	DOC PART 000	REVISION C	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION		DRAWING A3-SIZE		SERIES 218057		MATERIAL NUMBER SEE TABLE		CUSTOMER OTS		SHEET NUMBER 1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2021/12/07	09:22:43
-----------------	----	--------------	------------	----------