
# PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 50993	08/21	
			SEE PDM



## **MATERIAL:**

SIZE 8 STRAIGHT SOCKET CONNECTOR (9351-40046) MCX STRAIGHT CRIMP PLUG CONNECTORS:

RG-179/U CABLE (200-70-118) CABLE:

STRAIN RELIEF: M23053/5

### **PERFORMANCE:**

**IMPEDANCE:** 75 OHMS FREQ. RANGE: DC TO 3.0 GHz.

#### NOTES:

SIZE 8 SOCKET DESIGNED TO MATE TO SIZE 8 PIN CONTACT (9341-40064) ON 7093-0280, OR SIMILAR.
SIZE 8 SOCKET WILL NOT MATE TO STANDARD SIZE 8 PIN CONTACT OR BMA CONNECTOR.

MATERIAL: SEE NOTES FINISH: SEE NOTES SURFACE AREA: N/A **PROPRIETARY** THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' RACTIC.

DECIMAL: X ±.0.10
.XXX ±.010
.XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION

## UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 15T & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA: S. ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS

APPROVED:

DRAWN: TSW 08/26/21 CHECKED: SEE PDM

SEE PDM

MICROWAVE

SIZE 8 STR. SOCKET TO MCX STR. PLUG RG179 CABLE ASSEMBLY

SIZE DWG. NO. В

7093-0279