











REVISIONS						
ZONE	REV.	DESCRIPTION	DATE	BY	CHK	APPROVED
D2	-	INITAL RELEASE	12/9/2017	JAM	D2	



ISOMETRIC VIEW

GENERAL ENCLOSURE NOTES:

- ENCLOSURE MATERIAL MADE FROM LIGHT GRAY (RAL7035) HOT MOLDED FIBERGLASS REINFORCED POLYESTER.
- U.L. LISTED PER STD. 508 (FILE# E192121) PRIOR TO MODIFICATIONS.
- C.S.A. CERTIFIED PER STD. C22.2 No.94 (FILE# LR36508) PRIOR TO MODIFICATIONS.
- N.E.M.A. RATED TYPE 3, 3R, 4, 4X, 12 & 13 PRIOR TO MODIFICATIONS.
- I.E.C.-529 RATED IP66 PRIOR TO MODIFICATIONS.
- TEMPERATURE RANGES FROM -50°C TO 150°C.
- SELF EXTINGUISHING AND HALOGEN FREE.
- CABINETS ARE MAINTENANCE FREE & CORROSION RESISTANT.

 <p>THIS DRAWING USES THIRD ANGLE PROJECTION</p>	<u>UNLESS OTHERWISE SPECIFIED:</u> DIMENSIONS ARE IN INCHES		<u>SIGNATURE</u>		<u>DATE</u>		 <u>VYNCKIER</u> ENCLOSURE SYSTEMS INC.		
	<u>TOLERANCES:</u>		<u>DRAWN BY:</u> JAM		4/24/2018				
	<u>DECIMALS:</u> .X ± .030 .XX ± .020 .XXX ± .010		<u>ANGLES:</u> ± 1° <u>HOLE Ø:</u> ± .010		<u>CHECKED BY:</u> -		-		
	<p>REMOVE ALL BURRS BREAK ALL SHARP EDGES (MAX .005) (DIMENSIONS IN PARENTHESIS ARE SHOWN FOR REFERENCE)</p>		<u>DESIGN BY:</u> -		-		<p>VJ SERIES VYNCKIER PART# VJ806W</p>		
<u>FSCM No.</u> -									
<u>FINISH</u> NONE				<u>SIZE</u> C		<u>DWG No.</u> VJ806W			
						<u>REV.</u> -			
				<u>SCALE: NONE</u>		<u>SHEET: 1 OF 1</u>			