






RoHS Compliant




SECTION VIEW:A-A



VIEW:D SC 3:1

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	12/27'21	First release	PansLee
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				



ZTC 200 03 0 000 G

200 200A 03 3P Any special item by customer request 000 @Mark G: RoHS compliant (lead<4%) In copper Alloy

5	导电片/BUS BAR	—	3	黄铜BRASS (H59)	镀镍/NICKEL PLATING
4	M8 组合螺丝/SCREW	M8*16	6	钢STEEL	镀锌/镀锌/镀锌
3	ZTC 200 本体/BODY	—	1	PC BLACK	UL94-V0
2	标记条/MARKER BAR	0.5*9*128.5	1	PVC WHITE	—
1	ZTC 200 透明盖/COVER	—	1	PC TRANSPARENT BLUE	UL94-V2
序号/NO	名称/NAME	规格型号/SPECIFICATIONS	数量/Q.TY	材料/MATERIALS	备注/REMARK

標準 / IEC STANDARD: IEC60947-7-1
額定電壓 / RATED VOLTAGE: 660 V
額定電流 / CURRENT RATING: 200A
耐高壓 / WITHSTAND VOLTAGE: 2.5KV/Min
絕緣電阻 / INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 1000 V
工作溫度 / OPERATING TEMPERATURE RANG: -20 °C ~ +105°C
螺絲型號 / SCREW TYPE/扭力值 / TORQUE VALUE: M8 /16.9 N.m Max.
線徑範圍 / WIRE RANGE: 25-70mm²
重點尺寸 / Critical dimension: ▲


一般公差/TOLERANCES

尺寸/DIM(mm)	公差/TOL(mm)
0--10	±0.2
>10--20	±0.3
>20--30	±0.4
>30--40	±0.52
>40--50	±0.56
>50--65	±0.64
>65--85	±0.76
角度/ANGLE	±1°

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	ZTC 200-3P					
PART NO.	ZTC200030000G			DWG NO.	8ZTC0007-200	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		PansLee 2021.12.27	PansLee 2021.12.27		UNIT: mm	
					SCALE: NONE	
					SHEET: 01/01	
					REV: B	