





RoHS Compliant

PIN	2P	3P	4P	5P	6P	7P	8P	9P	10P
长度L	76.1	111.8	147.5	183.2	218.9	254.6	290.4	326.1	361.8

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	12/27'21	First release	PansLee
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				



ZBC	200	XX	0	000	G
200	200A	02	2P	000	@Mark
		03	3P		
		04	4P		
		05	5P		
		06	6P		
		07	7P		
		08	8P		
		09	9P		
		10	10P		
					G: RoHS compliant (lead<4%) In copper Alloy

7	鋼筒/CYLINDER	D5	1	鋼/STEEL	5P以上需要 /5P AND ABOVE IS NEEDED
6	防生片/COVER	0.5*69	1	PVC	—
5	标记条/MARKER BAR	Z-ZBN	1	PVC	—
4	端板/END PLATE	D-ZBC200A	1	PC	UL94 V-0
3	导电片/BUS BAR	DPRH-ZBC200	1*P	紫铜/PURE COPPER	鍍镍/NICKEL PLATING
2	螺丝/SCREW	M10*20	2*P	鋼/STEEL	鍍环保彩锌/ZINC PLATING
1	外壳/HOUSING	ZBC200A	1*P	PC	UL94 V-0
序号/NO	名称/NAME	规格型号/SPECIFICATIONS	数量/Q.TY	材料/MATERIALS	备注/REMARK

標準 / IEC STANDARD: IEC60947-7-1
額定電壓 / RATED VOLTAGE : 660 V
額定電流 / CURRENT RATING: 200A
工作溫度 / OPERATING TEMPERATURE RANG: -20 °C +105°C
螺絲型號 / SCREW TYPE/扭力值 / TORQUE VALUE: M10 / 6.0-8.0 N.m
線徑範圍 / WIRE RANGE: 70mm²
重點尺寸 / Critical dimension: ▲

一般公差/TOLERANCES	
尺寸/DIM(mm)	公差/TOL(mm)
0--10	±0.2
>10--20	±0.3
>20--30	±0.4
>30--40	±0.52
>40--50	±0.56
>50--65	±0.64
>65--85	±0.76
角度/ANGLE	±1°

Amphenol ANYTEK				CUSTOMER COPY	
TITLE ZBC 200A TERMINAL STRIP 2P-10P				ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD	
PART NO.	ZBC200XX0000G	DWG NO.	8ZBC0003-200		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		PansLee 2021.12.27	PansLee 2021.12.27		
				UNIT: mm	
				SCALE: NONE	
				SHEET: 01/01	REV.: B