





Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	12/27'21	First release	PansLee
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

PIN	2P	3P	4P	5P	6P	7P	8P	9P	10P
长度L	44.8	65.4	86	106.6	127.2	147.8	168.4	189	209.6



ZBC 060 XX 0 000 G

060 60A 02 2P 000 @Mark G: RoHS compliant (lead<4%) In copper Alloy

03 3P

04 4P

05 5P

06 6P

07 7P

08 8P

09 9P

10 10P

7	钢筒/CYLINDER	D5	1	钢/STEEL	SP以上需要/SP AND ABOVE IS NEEDED
6	防尘片/COVER	0.5*38	1	PVC	_____
5	标记条/MARKER BAR	Z-ZBN	1	PVC	_____
4	端板/END PLATE	D-ZBC60A	1	PC	UL94-V0
3	导电片/BUS BAR	DPH60A	1*P	黄铜/BRASS(H62)	镀镍/NICKEL PLATING
2	组合螺栓/SCREW	M6*12	2*P	钢/STEEL	镀环保彩锌/ZINC PLATING
1	外壳/HOUSING	ZBC60A	1*P	PC	UL94-V0
序号/NO	名称/NAME	规格型号/SPECIFICATIONS	数量/Q.TY	材料/MATERIALS	备注/REMARK

標準 / IEC STANDARD:	IEC60947-7-1
額定電壓 / RATED VOLTAGE :	660 V
額定電流 / CURRENT RATING:	60A
工作溫度 / OPERATING TEMPERATURE RANG:	-20 °C +105°C
螺絲型號 / SCREW TYPE/扭力值 / TORQUE VALUE:	M6 / 3.2-3.7 N.m
線徑範圍 / WIRE RANGE:	10mm ²
重點尺寸 / Critical dimension: ▲	

一般公差/TOLERANCES	
尺寸/DIM(mm)	公差/TOL(mm)
0--10	±0.2
10--20	±0.3
20--30	±0.4
>30--40	±0.52
>40--50	±0.56
>50--65	±0.64
角度/ANGLE	±1°

Amphenol **ANYTEK**

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		ZBC 60A TERMINAL STRIP 2P-10P					
PART NO.		ZBC060XX0000G		DWG NO.		8ZBC0001-60	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		PansLee 2021.12.27	PansLee 2021.12.27			UNIT: mm	
				SHEET: 01/01		SCALE: NONE REV: B	