





RoHS Compliant

PIN	2P	3P	4P	5P	6P	7P	8P	9P	10P
DIM L	58.5	85.7	112.7	139.6	166.7	193.8	220.9	248	275.1

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	12/27'21	First release	PansLee
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				



ZBC 100 XX 0 000 G

100 100A 02 2P 000 @Mark G: RoHS compliant (lead<4%) In copper Alloy

03 3P
04 4P
05 5P
06 6P
07 7P
08 8P
09 9P
10 10P

標準 / IEC STANDARD: IEC60947-7-1

額定電壓 / RATED VOLTAGE : 660 V

額定電流 / CURRENT RATING: 100A

工作溫度 / OPERATING TEMPERATURE RANG: -20 °C +105°C

螺絲型號 / SCREW TYPE/扭力值 / TORQUE VALUE: M8 / 4.0-4.5 N.m

線徑範圍 / WIRE RANGE: 25mm²

重點尺寸 / Critical dimension: ▲

一般公差/TOLERANCES	
角度/DIM(mm)	公差/TOL(mm)
0--10	±0.2
10--20	±0.3
20--30	±0.4
>30--40	±0.52
>40--50	±0.56
>50--65	±0.64
角度/ANGLE	±1°

9	銅筒/CYLINDER	D5	1	銅/STEEL	SP以上需要 /SP AND ABOVE IS NEEDED
8	防沖片/COVER	0.5*49	1	PVC	—
7	標記條/MARKER BAR	Z-RBN	1	PVC	—
6	端板/END PLATE	D-RBC100A	1	PC	UL94-V0
5	導電片/BUS BAR	DPH100A	1*P	黃銅/BRASS(H62)	鍍鎳/NICKEL PLATING
4	彈墊/SPRING WASHER	TD 8#	2*P	彈簧鋼/SPRING STEEL	鍍環保彩鋅/ZINC PLATING
3	平墊/FLAT GASKET	PD 8#	2*P	銅/STEEL	鍍環保彩鋅/ZINC PLATING
2	螺絲/SCREW	M8*12	2*P	銅/STEEL	鍍環保彩鋅/ZINC PLATING
1	外殼/HOUSING	ZBC100A	1*P	PC	UL94-V0
序号/NO	名稱/NAME	規格型號/SPECIFICATIONS	數量Q.TY	材料/MATERIALS	备注/REMARK

Amphenol ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD		
TITLE	ZBC 100A TERMINAL STRIP 2P-10P					
PART NO.	ZBC100XX0000G			DWG NO.	8ZBC0002-100	
PROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		PansLee 2021.12.27	PansLee 2021.12.27		UNIT: mm	
					SCALE: NONE	
				SHEET: 01/01	REV: B	