





RoHS Compliant



剖视图: A-A



VIEW:D SC 3:1



ZTC 300 04 0 000 G

300 300A 04 4P 000 @Mark G: RoHS compliant (lead<4%) In copper Alloy

標準 / IEC STANDARD:
額定電壓 / RATED VOLTAGE: 660 V
額定電流 / CURRENT RATING: 300A
耐高壓 / WITHSTAND VOLTAGE: 2.5KV/Min
絕緣電阻 / INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 1000 V
工作溫度 / OPERATING TEMPERATURE RANG: -20 °C ~ +105°C
螺絲型號 / SCREW TYPE/扭力值 / TORQUE VALUE: M10 /26 N.m Max.
線徑範圍 / WIRE RANGE: 70-150mm²
重點尺寸 / Critical dimension: ▲

IEC60947-7-1
660 V
300A
2.5KV/Min
1000 MΩ OR MORE AT DC 1000 V
-20 °C ~ +105°C
M10 /26 N.m Max.
70-150mm²

一般公差/TOLERANCES


尺寸/DIM(mm)	公差/TOL(mm)
0--10	±0.2
>10--20	±0.3
>20--30	±0.4
>30--40	±0.52
>40--50	±0.56
>50--65	±0.64
>65--85	±0.76
>85--100	±0.88
角度/ANGLE	±1°

5	导电片 / BUS BAR		4	黄铜 / BRASS (H59)	镀镍 / NICKEL PLATING
4	M10 组合螺丝/SCREW	M10*20	8	钢 / STEEL	镀锌/镀锌/ ZINC PLATING
3	ZTC 300 本体/BODY		1	PC BLACK	UL94-V0
2	标记条/MARKER BAR	0.5*9*215	1	PVC WHITE	
1	ZTC 300 透明盖/ COVER		1	PC TRANSPARENT BLUE	UL94-V2
序号/NO	名称/NAME	规格型号/SPECIFICATIONS	数量/Q.TY	材料/MATERIALS	备注/REMARK

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	ZTC 300-4P						
PART NO.	ZTC300040000G				DWG NO.	8ZTC0011-300	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		PansLee 2021.12.27	PansLee 2021.12.27		UNIT: mm		
					SCALE: NONE		
				SHEET: 01/01	REV.: B		