
REV	ECO	
A1	-	

MATERIAL SPECIFICATIONS

PROCESS SPECIFICATIONS

NEXT ASS'Y:

WEIGHT: 62g



	MIN. INSUL		TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
16	1.35 mm (.053 in)	2.62 mm (.103 in)	14-20 AWG (2.0-0.5mm²)	13 AMPS
12	2.46 mm (.097 in)	4.01 mm (.158 in)	10-14 AWG (6.0-2.0mm²)	25 AMPS

