

Order now

AHDP06-24-19SN-BRA 19 POSITIONS, PLUG, SOCKET, SHELL SIZE 24, STANDARD ARRANGEMENT, NORMAL DIAMETER SEAL, BACKSHELL RING ADAPTER (SNAP -ON). COMPARABLE TO PN# HDP26-24-19SN-L017

PART NUMBER: AHDP06-24-19SN-BRA

DATASHEET:  [View / Download \(pdf/datasheet/AHDP06-24-19SN-BRA.pdf\)](#)

SPECIFICATIONS:

- **Shell Size:** 24
- **No. of positions:** 19
- **Contact Size(s):** 12,16
- **Contact Type (Pin/Socket):** Socket
- **Contacts Included?:** No
- **Gender:** Female (Standard)
- **Wire Range:** 10-14 AWG (6.0-2.0mm²), 14-20 AWG (2.0-0.5mm²)
- **Amperage:** 25,13
- **Housing Material:** Thermoplastic
- **Voltage:** 250 V
- **Operating Temperature:** -55°C to +125°C
- **Color:** Black
- **IP Rating:** IP68 (1M of water for a period of 24 hours, in mated condition)IP69K (in mated condition)
- **Seal Material:** Silicone Rubber
- **Seal Diameter:** 3.40mm (.134") - 4.32mm (.170") / 2.50mm (.100") - 3.40mm (.134")
- **Seal Color:** Green
- **Rear Seal Type:** Normal
- **Dielectric Value:** Dielectric withstanding voltage less than 2 milliamps current leakage @ 1500 volts AC
- **Insulation Resistance:** 1000 Megaohm min @ 25°C
- **RoHS Compliant?:** Yes
- **Mating Cycle Durability:** >100
- **Mating Part*:** AHDP04-24-19P* & AHDP02-24-19P*

QUANTITY

1

+

-

 REQUEST A QUOTE

Like [Sign Up](#) to see what your friends like.

- Description

Description

AHDP06-24-19SN-BRA 19 Positions, Plug, Socket, Shell Size 24, Standard Arrangement, Normal Diameter Seal, Backshell Ring Adapter (Snap -on). Comparable to PN# HDP26-24-19SN-L017

RELATED ITEMS