

QUICKLY FIND WHAT YOU ARE LOOKING FOR USING OUR PRODUCT SELECTOR

| | | | | |
|--------------|---------------------|-------------|------------|------------|
| PRODUCT TYPE | NUMBER OF POSITIONS | IP RATING | AMPERAGE | MATERIAL |
| Search All | Search All | Search All | Search All | Search All |
| PRODUCT LINE | MAX VOLTAGE | APPLICATION | | |
| Search All | Search All | Search All | RESET | SEARCH |

Home (/) > Our Product Lines (/our-product-lines) > A Series (/a-series-connectors) > DuraMate Series (/duramate) > DuraMate AHDP (/duramate-ahdp) > Duramate AHDP 18-8 (/duramate-ahdp-18-8) > AHDP02-18-08PR-BRA 8 Positions, Sealed Panel Mount Receptacle, Pin, Shell Size 18, Standard Arrangement, Reduced Diameter Seal, Backshell Ring Adapter (Snap -on) (https://www.amphenol-sine.com/AHDP02-18-08PR-BRA-8-Positions-Sealed-Panel-Mount-Receptacle-Pin-Shell-Size-18-Standard-Arrangement-Reduced-Diameter-Seal-Backshell-Ring-Adapter-Snap-on_p_12567.html)



Click to expand

(assets/images/AHDP02-18-08PR-BRA.jpg)

AHDP02-18-08PR-BRA 8 Positions, Sealed Panel Mount Receptacle, Pin, Shell Size 18, Standard Arrangement, Reduced Diameter Seal, Backshell Ring Adapter (Snap -on)




(assets/images/AHDP02-18-08PR-BRA.jpg) (assets/images/AHDP02-18-08PR-BRA_2.jpg)

-
-

AHDP02-18-08PR-BRA 8 POSITIONS, SEALED PANEL MOUNT RECEPTACLE, PIN, SHELL SIZE 18, STANDARD ARRANGEMENT, REDUCED DIAMETER SEAL, BACKSHELL RING ADAPTER (SNAP-ON)

PART NUMBER: AHDP02-18-08PR-BRA

DATASHEET:  [View / Download \(pdf/datasheet/AHDP02-18-08PR-BRA.pdf\)](#)

SPECIFICATIONS:

- **Shell Size:** 18
- **No. of positions:** 8
- **Contact Size(s):** 12
- **Contact Type (Pin/Socket):** Pin
- **Contacts Included?:** No
- **Gender:** Male (Standard)
- **Wire Range:** 10-14 AWG (6.0-2.0mm²)
- **Amperage:** 25
- **Housing Material:** Thermoplastic
- **Voltage:** 250 V
- **Operating Temperature:** -55°C to +125°C
- **Color:** Black
- **IP Rating:** IP68 (1M of water for a period of 24 hours, in mated condition)IP69K (in mated condition)
- **Seal Material:** Silicone Rubber
- **Seal Diameter:** 2.46mm (.097") - 4.01mm (.158")
- **Seal Color:** Blue
- **Rear Seal Type:** Reduced diameter seal
- **Dielectric Value:** Dielectric withstanding voltage less than 2 milliamps current leakage @ 1500 volts AC
- **Insulation Resistance:** 1000 Megaohm min @ 25°C
- **RoHS Compliant?:** Yes
- **Mating Cycle Durability:** >100
- **Mating Part*:** AHDP06-18-08S*

QUANTITY

1

+

-

 REQUEST A QUOTE

Like [Sign Up](#) to see what your friends like.

- Description

Description

AHDP02-18-08PR-BRA 8 Positions, Sealed Panel Mount Receptacle, Pin, Shell Size 18, Standard Arrangement, Reduced Diameter Seal, Backshell Ring Adapter (Snap -on)

RELATED ITEMS