



Additional coding
View in direction B





C1TBATO-H005PN-0000
Material-ID: 50294714
Mechanical coding: B
Color coding: red


Only insert
View in direction A
3:1




Color coding
Keying indication



C1TAATO-H005PN-0000
Material-ID: 50294706
Mechanical coding: A
Color coding: light brown




C1TCA TO-H005PN-0000
Material-ID: 50294715
Mechanical coding: C
Color coding: blue



Delivery condition
1:1

Pin 2)
6:1



Technical informations:

- Current load: 13A (with AWG16) acc. to SAE-AS39029D
- Rated voltage: <50 V AC / <75 V DC (SELV acc. IEC 61140:2016) 1)
- Test voltage: 1800 V AC (acc. EIA-364-20F:2019, sea level)
- For technical informations, materials and surfaces see datasheet D00016301
- For useable accessories see datasheet D00016302
- For an assembly instruction see datasheet D00016303

1) In case that other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid.

2) For further contact information and crimping instructions see datasheet D00016300

All datasheets available at www.odu.de

Bei den hier dargestellten ODU-Steckverbindern handelt es sich nach DIN EN 61984:2009 um Steckverbinder ohne Schaltleistung (COC) !
/the pictured ODU-connectors are in relation to DIN EN 61984:2009 connectors without switching capacity (COC) !

Contact	Material-ID	Wire Size
#16	50267258	AWG 16-20

 Allgemeintoleranz/general tol.: DIN ISO 2768-mH Tolerierung / Tolerancing: DIN ISO 8015		Benennung/description: Threaded Plug AMC Series T		Werkstoff: material: see BOM
				Maßstab: scale: 2:1
Status/state: Approved	Version: revision: -	Zeichnungs-Nr.: Drawing-Id.: 00190570		Format: size: A3
Erstellt/prepared 22.10.2020 jaigner	Geaendert/revised 22.10.2020 jaigner	Material-Nr.: Material-Id.: C1T_ATO-H005PN-0000		Einheit: dim.: mm
Freigabe/released 22.04.2021 chobmaier	ODU-MUEHL DORF Datum/date	Name/name		Bl.: sheet: 1