

| P | LTR | DESCRIPTION        | DATE      | DWN | APVD |
|---|-----|--------------------|-----------|-----|------|
|   | A   | PRODUCTION RELEASE | 19JAN2022 | SCB | PS   |
|   |     |                    |           |     |      |
|   |     |                    |           |     |      |




NOTES:

1 MATERIALS & FINISH  
HOUSING : PA66, UL94 V0, COLOR - LIGHT GREEN  
CONTACT : COPPER ALLOY, TIN PLATED


2. ELECTRICAL  
RATED VOLTAGE : 300V  
RATED CURRENT : 10A  
INSULATION RESISTANCE : >2000 M Ohm (500V DC)

3. OPERATING TEMPERATURE RANGE : -40°C TO +105°C


4 TOLERANCE NOT CUMULATIVE



|       |            |             |
|-------|------------|-------------|
| 76.81 | 20         | 2-2385006-0 |
| 73.00 | 19         | 1-2385006-9 |
| 69.19 | 18         | 1-2385006-8 |
| 65.38 | 17         | 1-2385006-7 |
| 61.57 | 16         | 1-2385006-6 |
| 57.76 | 15         | 1-2385006-5 |
| 53.95 | 14         | 1-2385006-4 |
| 50.14 | 13         | 1-2385006-3 |
| 46.33 | 12         | 1-2385006-2 |
| 42.52 | 11         | 1-2385006-1 |
| 38.71 | 10         | 1-2385006-0 |
| 34.90 | 9          | 2385006-9   |
| 31.09 | 8          | 2385006-8   |
| 27.28 | 7          | 2385006-7   |
| 23.47 | 6          | 2385006-6   |
| 19.66 | 5          | 2385006-5   |
| 15.85 | 4          | 2385006-4   |
| 12.04 | 3          | 2385006-3   |
| 8.23  | 2          | 2385006-2   |
| DIM A | NO. OF POS | TE PN       |



2385006-3 AS SHOWN

|                                                                                                         |  |                                                                            |                                                                                                       |                         |  |
|---------------------------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------|-------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                  |  | DWN 12JAN2022<br>SHRICHARANA B                                             |  TE Connectivity |                         |  |
| DIMENSIONS:<br>mm                                                                                       |  | CHK 12JAN2022<br>SUBHASREE S                                               |                                                                                                       |                         |  |
|                    |  | APVD 12JAN2022<br>PRASHANTH S                                              |                                                                                                       |                         |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC<br>1 PLC<br>2 PLC<br>3 PLC<br>4 PLC<br>ANGLES<br>FINISH |  | PRODUCT SPEC<br>108-32299<br>APPLICATION SPEC<br>114-32242<br>WEIGHT<br>-  |                                                                                                       |                         |  |
| MATERIAL<br>1                                                                                           |  | NAME<br>TERMINAL BLOCK, 180 DEG HEADER,<br>PITCH 3.81mm, TAIL LENGTH 3.4mm |                                                                                                       | RESTRICTED TO<br>-      |  |
|                                                                                                         |  | SIZE<br>A3                                                                 | CAGE CODE<br>00779                                                                                    | DRAWING NO<br>C-2385006 |  |
| CUSTOMER DRAWING                                                                                        |  | SCALE<br>5:1                                                               | SHEET<br>1 OF 1                                                                                       | REV<br>A                |  |